33466 ✔ ACTIVE

SOLISTRAND

TE Internal #: 33466

Closed Ring Tongue Terminal, 6 AWG, 5/16 / M8 Stud, 8.33 mm [.328 in] Stud Diameter, Closed Barrel, Straight, Tin Plating, Uninsulated

View on TE.com >

Terminals & Splices > Ring Terminals







Ring Terminal Product Type: **Closed Ring Tongue Terminal**

Wire Size: **20800 – 33100 CMA**

Stud Size: **5/16, M8**

Features

Product Type Features

Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	5/16, M8
Sealable	No
Wire Insulation Support Retention Type	Non-Insulation Support

Configuration Features

Number of Holes	1

Contact Features

Barrel Type	Closed
Terminal Orientation	Straight
Terminal Plating Material	Tin

Mechanical Attachment

Wire Insulation Support	Without

Dimensions

Wire Size	20800 – 33100 CMA
Stud Diameter	8.33 mm[.328 in]

Downloaded from Arrow.com.

Tongue Thickness	1.45 mm[.057 in]
Product Length	31.65 mm[1.246 in]
Barrel Inside Diameter	5.89 mm[.232 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	0 – 170 °C[0 – 338 °F]

Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin

Industry Standards

Government Qualified Terminal	No

Packaging Features

Packaging Quantity	100
Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous


Downloaded from Arrow.com.

materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach


Compatible Parts



TE Part # 2-1377172-2
SMP 0-0033466-0



TE Part # 600850
ROTO-CRIMP TOOL (ASI)




TE Part # 48128
HYP8 SOLIS 6AWG NEST




TE Part # 8-33466-3
TERMINAL,SOLIS R 6 5/16



TE Part # 601075
BANTAM ROTA-CRIMP TOOL



TE Part # 1901000-1
NEST #6



TE Part # 1901002-1
INDENTER, SOLISTRAND



TE Part # 1490414-2
HYP10 SOLIS HD 6-4AWG INDENTER



TE Part # 48127
HYP8 SOLIS 6-2AWG INDENTER



TE Part # 2-33466-3
TERMINAL,SOLIS R 6 5/16



TE Part # 2-33466-1
SOLISTRAND RING 6 5/16



TE Part # 1490413-2
HYP10 SOLIS HD 8AWG NEST



TE Part # 69217
HYP8/10 SOLIS 6AWG DIE SET

Customers Also Bought

Downloaded from Arrow.com.




TE Part #36815
TERMINAL,SOLIS R 4 3/8



TE Part #160032
SOLIS 6 R 10MM



TE Part #321298
TERMINAL,SOLIS R 6 10




TE Part #321580
TERMINAL,SOLIS FLAG R 1/0 5/16




TE Part #321598
TERMINAL,SOLIS R 6 1/4




TE Part #321875
TERMINAL,SOLIS R 3/0 3/8



TE Part #322215
TERMINAL,SOLIS FLAG R 1/0 1/4



TE Part #770068-1
02P .093 COMM P&S PLUG .248CL



TE Part #2392559-3
SOC CONN CVR,3POS,DIA 4MM,ICT CVE



TE Part #1-2392563-2
3POS,SOC INNER HSG,DIA 4MM, COD A,CVE

Documents

Product Drawings

TERMINAL,SOLIS R 6 5/16

English

CAD Files

Customer View Model

ENG_CVM_CVM_33466_AP.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_33466_AP.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_33466_AP.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

Downloaded from Arrow.com.

SOLISTRAND - QRG

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Agency Approvals

UL Report

English

UL Report

English

Downloaded from Arrow.com.