
**Part Number :** 14601201
**Product Description :** 2.54mm Pitch SL Insulation Displacement Connector Assembly, Female, Single Row, Version C, Front Ribs, Wire Size 28 AWG, 3.81µm Tin/Lead (SnPb), 20 Circuits
**Series Number :** 70400
**Status :** Active
**Product Category :** Connector Housings
**Engineering Part Number :** 70400-0404



## Documents and Resources

### Drawings

014601201_sd.pdf

PK-70873-0001-001.pdf

### 3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

### Specifications

PS-70400-001.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Reviewed |
| China RoHS | Not Reviewed |
| EU ELV | Not Reviewed |
| Low-Halogen Status | Not Reviewed |
| REACH SVHC | Not Reviewed |
| EU RoHS | Not Reviewed |

Compliance Statements

- EU RoHS
- REACH SVHC

Downloaded from Arrow.com.

- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Connector Housings |
| Series | 70400 |
| Description | 2.54mm Pitch SL Insulation Displacement Connector Assembly, Female, Single Row, Version C, Front Ribs, Wire Size 28 AWG, 3.81µm Tin/Lead (SnPb), 20 Circuits |
| Comments | Terminals Preloaded |
| Component Type | Housing |
| Product Name | SL |
| UPC | 800753767652 |

### Agency

| | |
|---|---|
| CSA | LR19980 |
| UL | E29179 |

### Electrical

| | |
|---|---|
| Voltage - Maximum | 250V |

### Physical

| | |
|---|---|
| Circuits (Loaded) | 20 |

Downloaded from Arrow.com.

| | |
|---|---|
| Circuits (maximum) | 20 |
| Color - Resin | Black |
| Durability (mating cycles max) | 25 |
| Entry Angle | Vertical |
| Flammability | 94V-0 |
| Gender | Female |
| Glow-Wire Capable | No |
| Lock to Mating Part | No |
| Material - Metal | Phosphor Bronze |
| Material - Plating Mating | Tin |
| Material - Plating Termination | Tin |
| Material - Resin | Polyester |
| Number of Rows | 1 |
| Packaging Type | Tube |
| PCB Retention | No |
| Pitch - Mating Interface | 2.54mm |
| Plating min - Mating | 3.810µm |
| Plating min - Termination | 3.810µm |
| Polarized to Mating Part | Yes |
| Stackable | Yes |
| Temperature Range - Operating | -40° to +105°C |
| Termination Interface Style | IDT or Pierce |
| Wire/Cable Type | Discrete Wire, Ribbon Cable |
| Wire Insulation Diameter | 1.35mm max. |
| Wire Size (AWG) | 28 |

## Application Tooling

### Global

| Description | Part Number |
|---|---|
| Ribbon Cable Tool Kit, Press Not Included | 622016600 |



Downloaded from Arrow.com.