



Part Number : [357450210](#)

Product Description : VersaBlade Male Crimp
Terminal, 18-14 AWG, Type A

Series Number : 35745

Status : Active

Product Category : Crimp Terminals



Documents and Resources

Drawings

[357450210_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[351500000AS_ENG-000.pdf](#)

[351500000AS_KOR-000.pdf](#)

[PK-35745-001-001.pdf](#)

[PS-35150-001-001.pdf](#)

[351800400-001.pdf](#)

[351800600-001.pdf](#)

Tooling Specifications

[CS-35745-001-001.pdf](#)

[CS-35745-001-002.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21

REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	35745
Description	VersaBlade Male Crimp Terminal, 18-14 AWG, Type A
Application	Power, Wire-to-Wire
Product Name	VersaBlade
UPC	800754378444

Physical

Durability (mating cycles max)	30
Gender	Male
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.320/g

Packaging Type	Reel
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	3.40mm max.
Wire Size (AWG)	14, 16, 18
Wire Size mm ²	0.85-2.00

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Use with Part(s)

Description	Part Number
VersaBlade Hybrid Plug Housing, 3 Circuits, Positive Lock, Natural	<u>351510310</u>
VersaBlade Hybrid Plug Housing, 3 Circuits, Positive Lock, Blue	<u>351510314</u>
VersaBlade Hybrid Plug Housing, 3 Circuits, Positive Lock, Natural, Glow-Wire Capable	<u>351510319</u>
VersaBlade Hybrid Plug Housing, 4 Circuits, Positive Lock, Natural	<u>351510410</u>
VersaBlade Hybrid Plug Housing, 4 Circuits, Positive Lock, Red	<u>351510412</u>
VersaBlade Hybrid Plug Housing, 4 Circuits, Positive Lock, Blue	<u>351510414</u>
VersaBlade Hybrid Plug Housing, 4 Circuits, Positive Lock, Natural, Glow-Wire Capable	<u>351510419</u>
VersaBlade Hybrid Plug Housing, 6 Circuits, Positive Lock, Natural	<u>351510610</u>
VersaBlade Hybrid Plug Housing, 6 Circuits, Positive Lock, Blue	<u>351510614</u>
VersaBlade Hybrid Plug Housing, 6 Circuits, Positive Lock, Natural, Glow-Wire Capable	<u>351510619</u>
VersaBlade Hybrid Plug Housing, 3 Circuits, Positive Lock, Yellow, Glow-Wire Capable	<u>351513319</u>

VersaBlade Hybrid Plug Housing, 4 Circuits, Positive Lock, Yellow, Glow-Wire Capable	<u>351513419</u>
VersaBlade Hybrid Plug Housing, 6 Circuits, Positive Lock, Yellow, Glow-Wire Capable	<u>351513619</u>
VersaBlade Hybrid Plug Housing, 3 Circuits, Positive Lock, Blue, Glow-Wire Capable	<u>351514319</u>
VersaBlade Hybrid Plug Housing, 4 Circuits, Positive Lock, Blue, Glow-Wire Capable	<u>351514419</u>
VersaBlade Hybrid Plug Housing, 6 Circuits, Positive Lock, Blue, Glow-Wire Capable	<u>351514619</u>
VersaBlade Multi-Module 2-3-4 Hybrid Receptacle Housing, 9 Circuits, Full Flange Panel Mount, Natural, Glow-Wire Capable	<u>2026500909</u>
VersaBlade Multi-Module 2-2 Hybrid Receptacle Housing, without Mounting Ears, 4 Circuits, Natural, Glow-Wire Capable	<u>2041020429</u>
VersaBlade Multi-Module 4-2 Hybrid Receptacle Housing, 6 Circuits, Natural, Glow-Wire Capable	<u>2041020609</u>
VersaBlade Multi-Module Hybrid Plug Housing, 4 Circuits, Friction Lock, Natural, Glow-Wire Capable	<u>2041020409</u>
VersaBlade Multi-Module Hybrid Plug Housing, 4 Circuits, Positive Lock, Natural, Glow-Wire Capable	<u>2041020419</u>
VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Friction Lock, Type B, Natural	<u>351810210</u>
VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Friction Lock, Type B, Blue	<u>351810214</u>
VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Positive Lock, Type B, Natural, Glow-Wire	<u>359659210</u>

Capable	
VersaBlade Multi-Module Hybrid Plug Housing, 2 Circuits, Positive Lock, Type B, Yellow, Glow-Wire Capable	<u>359659213</u>
VersaBlade Hybrid Receptacles Housings and TPAs	<u>35150</u>
VersaBlade Multi-Module Hybrid Receptacle Housings	<u>35180</u>
VersaBlade Multi-Module 2-3-4 Hybrid Receptacle Housings	<u>35524</u>

Application Tooling

Global

Description	Part Number
Extraction and Activation Tool	<u>638132700</u>
Hand Crimp Tool for 1.80mm-Wide Crimp Terminals	<u>638190600</u>
FineAdjust Applicator for Male and Female VersaBlade Crimp Terminals, 18-14 AWG Wire with Insulation Diameter 2.80-3.40mm for IPC Class 2	<u>638629100</u>

This document was generated on Apr 30, 2026