




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
E		REVISED PER ECR-24-226486	20NOV2024	TB	JP

1. PINS TO COMPLY WITH AMP SOLDERABILITY SPEC. 109-11-3.

2. 0.00381 MIN MATTE TIN OVER
0.00127 MIN NICKEL.

3. MATES WITH PART P/N 1586592-1.

4. 0.00076 MIN GOLD PLATE IN THE LOCALIZED
GOLD PLATE AREA 0.00381 MIN MATTE TIN
IN THE LOCALIZED TIN PLATE AREA, BOTH
OVER 0.00127 MIN NICKEL.

RECOMMENDED MOUNTING HOLE PATTERN
FOR 1.57 THICK P.C. BOARD

OBSOLETE	BRASS, TIN 4	NYLON, 94V-0, WHITE	1586600-2
	BRASS, TIN 2	NYLON, 94V-0, WHITE	1586600-1
	PIN CONTACT MATERIAL AND FINISH HOUSING MATERIAL AND COLOR PART NUMBER		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER 08APR2005	TE Connectivity	
		CHK C. JONES 08APR2005		
DIMENSIONS: mm		APVD C. JONES 08APR2005	NAME	
			HDR ASMBLY,14 CIR, DBL ROW VERTICAL, SPEC KEYING, MINI-UNIVERSAL MATE-N-LOK(TM)	
			APPLICATION SPEC	
			SIZE	CAGE CODE
			A1	00779
			WEIGHT	—
			CUSTOMER DRAWING	SCALE
			NA	SHEET
			1	OF
			1	REV
			E	