



+ RELAYS, CONTACTORS & SWITCHES
PROTECTIVE RELAYS



✓ Active

TE CONNECTIVITY (TE)
WUV-48DC=DC UNDERVOLTAGE RELAY
CII | WUVDC

WUV-48DC
TE Internal Number: 8-1618112-2

Not EU RoHS Compliant
Not EU ELV Compliant
Contact Arrangement 1 Form A, SPST-NO, 1 NO
Contact Current Rating (A) 5
Input Voltage (VDC) 48
Time Delay Without
Phase Single, Three

DOCUMENTATION

No documentation available.

FEATURES

Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features

Protection Function Undervoltage
Time Delay Without
Phase Single, Three
Product Type Relay
Relay Type Protective Relay

Electrical Characteristics

Input Voltage (VDC) 48
Actuating System DC

Signal Characteristics

Frequency Adjustment (Hz) 50 – 400

Contact Features

- Type of Control Potentiometer Adjustable
- Contact Arrangement 1 Form A, SPST-NO, 1 NO
- Contact Current Rating (A) 5
- Contact Arrangement (Additional Output) 1 Form B, SPST-NC, 1 N/C

Dimensions

Dimensions (L x W x H) (Approximate) 88.9 x 98.29 x 76.2 mm [3.5 x 3.87 x 3 in]

Usage Conditions

Operating Temperature Range (°C) -20 – 65

Operation/Application

Mode of Operation Adjustable Drop-Out

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance
PDF