



DRAWING REVISIONS (RELEASE DATE ON FILE)			
REV	DOCUMENT	APP	APPROVAL DATE
E	PER C.O.# 851	V.R.	02/09/10







REAR VIEW



NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN [ ] ARE IN INCHES.
2. FOR WIRE SIZE APPLICATION, CONSULT FACTORY.
3. FEMALE TERMINAL ORDERED SEPARATELY: 425 00 00 873/872.
4. MATES WITH CINCH HEADER CONNECTOR (CONSULT FACTORY).
5. SEAL PLUG ORDERED SEPARATELY: 581 00 00 011.
6. TOLERANCES UNLESS OTHERWISE SPECIFIED:
   .X ±0.5
   .XX ±0.25
7. SEALING RANGE FOR WIRE INSULATION DIA.;
   MAX 2.64MM (.104"), MIN 1.96MM (.077").
8. A TRIANGLE ▲ INDICATES CRITICAL FUNCTION DIMENSION.
9. IF TIE-WRAP DRESSING CONDUCTORS, CINCH RECOMMENDS A SPACING
   OF NO LESS THAN 2 INCHES BEHIND THE BACK PLATE.

UNITS: METRIC	PRO/E	CINCH	MODELED BY: J. DRYE
DO NOT SCALE DRAWING	DESIGN ENGINEER: A. CAINES	DATE: 5/03/01	1700 FINLEY RD LOMBARD, IL. 60148
UNLESS OTHERWISE SPECIFIED: ALL DIMENSIONS ARE IN mm	APPROVALS ON FILE	TITLE: CONNECTOR ASSEMBLY SOCKET 30 POSITION	
		MATERIAL: SEE VIEW	CONTROL SPEC NUMBER: POLAR A
		MATERIAL SPEC NUMBER / FINISH	PROJECT NUMBER: A14243
		CAD FILE NUMBER: 5810130027S	DRAWING NUMBER: 5810130027S
		CAGE IDENT NO.: 71785 / SIZE: B	SCALE: 1.000 / SHEET 1 OF 1

CONFIDENTIAL
THIS DOCUMENT IS THE PROPERTY OF CINCH. NEITHER THIS DOCUMENT NOR ANY OF THE INFORMATION CONTAINED IN IT MAY BE DUPLICATED OR DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF CINCH.
©COPYRIGHT 2009 CINCH

Downloaded from Arrow.com.
Please read our datasheet & drawing disclaimer here.