

Johanson Product Information for 501S42E300FV3E

Johanson Company: Johanson Technology inc. Product Release Date: 18 January, 2006

Deprecated P/N: 501S42E300FV3E

Datasheet Date: 08-11-2024

Description: Capacitors High-Q MLC E-Series,
1111, Hi-Q NP0/C0G, 500V, 30pF \pm 1%, Ni/Sn
(RoHS), 7" Reel Embossed Tape

Life Cycle Stage: Active - Production

Schedule B: 8532

ECCN: EAR99

RoHS Compliance: Yes, RoHS 10/10

REACH: 1

Country of Origin: US

Product Family: Capacitors

Product Subfamily: Capacitors High-Q MLC E-
Series

Capacitance Value: 30.000

Cap Unit of Meas: pF

Tolerance: \pm 1%

Voltage: 500.0

Dielectric Temp Coefficient: Hi-Q NP0/C0G

Termination: 68

Marking: Cap Code & Tol

Web Page Link:

<https://www.johansontechnology.com/S42E>

Size for Capacitors (EIA): 1111

Specification Number: 35S0144B

Thickness (Max): 0.102

End Band (Min):

End Band (Max):

Standard Item: 1

Lead Time Typical (Weeks)*:

*This can vary significantly so it is important
to obtain a quotation with lead time for
production planning purposes. 10

Length (Min): 0.100

Length (Max): 0.130

Width (Min): 0.095

Width (Max): 0.125

Packaged Weight (lb) Arm: 0.45

Packaging: 7" Reel Embossed Tape

Packaging Qty: 2000

Operating Temp Range: -55°C to +150°C

Storage Temp Range (Packaged): -65°C to
+150°CStorage Temp Range (Non Operating): +5°C to
+40°C with RH 20% to 70%