

AD7501/AD7502/AD7503

FEATURES

DTL/TTL/CMOS Direct Interface

Power Dissipation: 30 μ W

R_{ON} : 170 Ω

Standard 16-Lead DIPs and 20-Terminal Surface Mount Packages

GENERAL DESCRIPTION

The AD7501 and AD7503 are monolithic CMOS, 8-channel analog multiplexers which switch one of eight inputs to a common output, depending on the state of three binary address lines and an "enable" input. The AD7503 is identical to the AD7501 except its "enable" logic is inverted. All digital inputs are TTL/DTL and CMOS logic compatible.

The AD7502 is a monolithic CMOS dual 4-channel analog multiplexer. Depending on the state of two binary address inputs and an "enable," it switches two output buses to two of eight inputs.

Truth Tables


AD7501

A_2	A_1	A_0	EN	"ON"
0	0	0	1	1
0	0	1	1	2
0	1	0	1	3
0	1	1	1	4
1	0	0	1	5
1	0	1	1	6
1	1	0	1	7
1	1	1	1	8
X	X	X	0	None


AD7503

A_2	A_1	A_0	EN	"ON"
0	0	0	0	1
0	0	1	0	2
0	1	0	0	3
0	1	1	0	4
1	0	0	0	5
1	0	1	0	6
1	1	0	0	7
1	1	1	0	8
X	X	X	1	None

FUNCTIONAL BLOCK DIAGRAM AD7501/AD7503



AD7502



AD7502

A_1	A_0	EN	"ON"
0	0	1	1 & 5
0	1	1	2 & 6
1	0	1	3 & 7
1	1	1	4 & 8
X	X	0	None

REV. B

Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties that may result from its use. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices. Trademarks and registered trademarks are the property of their respective companies.

One Technology Way, P.O. Box 9106, Norwood, MA 02062-9106, U.S.A.
Tel: 781/329-4700 www.analog.com
Fax: 781/326-8703 © 2003 Analog Devices, Inc. All rights reserved.

AD7501/AD7502/AD7503—SPECIFICATIONS ($V_{DD} = +15\text{ V}$, $V_{SS} = -15\text{ V}$ unless otherwise noted.)

Parameter	Version ¹	Switch Condition	@ +25°C		Over Specified Temperature Range		Test Conditions
			AD7501, AD7503	AD7502	AD7501, AD7503	AD7502	
ANALOG SWITCH							
R _{ON}	All	ON	170 Ω typ, 300 Ω max	170 Ω typ, 300 Ω max			−10 V ≤ V _S ≤ +10 V
R _{ON} vs. V _S	All	ON	20% typ	20% typ			I _S = 1.0 mA
R _{ON} vs. Temperature	All	ON	0.5%/°C typ	0.5%/°C typ			V _S = 0 V, I _S = 1.0 mA
ΔR _{ON} Between Switches	All	ON	4% typ	4% typ			
R _{ON} vs. Temperature Between Switches	All	ON	± 0.01%/°C	± 0.01%/°C			
I _S	K	OFF	0.2 nA typ, 2 nA max	0.2 nA typ, 2 nA max	50 nA max	50 nA max	V _S = −10 V, V _{OUT} = +10 V and
I _{OUT}	S	OFF	0.5 nA max	0.5 nA max	50 nA max	50 nA max	V _S = +10 V, V _{OUT} = −10 V
	K	OFF	1 nA typ, 10 nA max	0.6 nA typ, 5 nA max	250 nA max	125 nA max	V _S = −10 V, V _{OUT} = +10 V and
I _{OUT} − I _S							V _S = +10 V, V _{OUT} = −10 V
	S	OFF	5 nA max	3 nA max	250 nA max	125 nA max	AD7501/02: Enable LOW
	K	ON	12 nA max	7 nA max	300 nA max	175 nA max	AD7503: Enable HIGH
	S	ON	5.5 nA max	3.5 nA max	300 nA max	175 nA max	V _S = 0
DIGITAL CONTROL							
V _{INL}	All				0.8 V max	0.8 V max	
V _{INH}	All				2.4 V min	2.4 V min	
I _{INL} or I _{INH}	All		10 nA typ	10 nA typ			
C _{IN}	All		3 pF typ	3 pF typ			
DYNAMIC CHARACTERISTICS							
t _{ON}	All		0.8 μs typ	0.8 μs typ			V _{IN} = 0 to +5.0 V
t _{OFF}	All		0.8 μs typ	0.8 μs typ			(See Test Circuit 2)
C _S	All	OFF	5 pF typ	5 pF typ			
C _{OUT}	All	OFF	30 pF typ	15 pF typ			
C _{SOUT}	All	OFF	0.5 pF typ	0.5 pF typ			
C _{SS} Between Any Two Switches	All	OFF	0.5 pF typ	0.5 pF typ			
POWER SUPPLY							
I _{DD}	All		500 μA max	500 μA max	500 μA max	500 μA max	All Digital Inputs Low
I _{SS}	All		500 μA max	500 μA max	500 μA max	500 μA max	
I _{DD}	All		800 μA max	800 μA max	800 μA max	800 μA max	All Digital Inputs High
I _{SS}	All		800 μA max	800 μA max	800 μA max	800 μA max	

NOTES

¹KN version specified for 0°C to +70°C, KQ version for -25°C to +85°C; and SQ, SE versions for -55°C to +125°C.

Specifications subject to change without notice.

ABSOLUTE MAXIMUM RATINGS

($T_A = +25^{\circ}\text{C}$ unless otherwise noted)

V_{DD} to GND +17 V

V_{SS} to GND -17 V

V Between Any Switch Terminals¹ 25 V

Digital Input Voltage Range V_{DD} to GND

Overvoltage at V_{OUT} (V_S) V_{SS} , V_{DD}

Switch Current (I_S , Continuous One Channel) 35 mA

Switch Current (I_S , Surge One Channel)

1 ms Duration, 10% Duty Cycle 50 mA

Power Dissipation (Any Package)

Up to +75°C 450 mW

Derates above +75°C by 6 mW/°C

Operating Temperature

Commercial (KN Version) 0°C to +70°C

Industrial (KQ Version) -25°C to +85°C

Extended (SQ, SE Versions) -55°C to +125°C

Storage Temperature -65°C to +150°C

Lead Temperature (Soldering, 10 sec) +300°C

CAUTION

¹Do not apply voltages higher than V_{DD} and V_{SS} to any other terminal, especially when $V_{SS} = V_{DD} = 0\text{ V}$ all other pins should be at 0 V.

²The digital control inputs are diode protected; however, permanent damage may occur on unconnected units under high energy electrostatic fields. Keep unused units in conductive foam at all times.

CAUTION

ESD (electrostatic discharge) sensitive device. Electrostatic charges as high as 4000 V readily accumulate on the human body and test equipment and can discharge without detection. Although the AD7501, AD7502, and AD7503 feature proprietary ESD protection circuitry, permanent damage may occur on devices subjected to high energy electrostatic discharges. Therefore, proper ESD precautions are recommended to avoid performance degradation or loss of functionality.



ORDERING GUIDE

Model ¹	Temperature Range	Package Options ²
AD7501KN	0°C to +70°C	N-16
AD7501KQ	-25°C to +85°C	Q-16
AD7501SQ	-55°C to +125°C	Q-16
AD7501SE	-55°C to +125°C	E-20A
AD7502KN	0°C to +70°C	N-16
AD7502KQ	-25°C to +85°C	Q-16
AD7502SQ	-55°C to +125°C	Q-16
AD7502SE	-55°C to +125°C	E-20A
AD7503KN	0°C to +70°C	N-16
AD7503KQ	-25°C to +85°C	Q-16
AD7503SQ	-55°C to +125°C	Q-16
AD7503SE	-55°C to +125°C	E-20A


NOTES

¹To order MIL-STD-883, Class B processed parts, add/883B to part number.

See the Analog Devices' 1990 Military Databook for military data sheet.

²E = LCC; N = PDIP; Q = CERDIP.

PIN CONFIGURATIONS



Typical Performance Characteristics

1. R_{ON} Versus V_S




Figure 1a. R_{ON} vs. V_S At Different Power Supplies




Figure 2a. Digital Threshold Voltage (V_{INH} , V_{INL}) vs. Power Supply




Figure 3. t_{ON} , t_{OFF} vs. Digital Input Voltage




Figure 1b. R_{ON} vs. V_S At Different Temperatures




Figure 2b. Digital Threshold Voltage (V_{INH} , V_{INL}) vs. Temperature





Figure 4. Power Dissipation vs. Logic Frequency (50% Duty Cycle)


AD7501/AD7502/AD7503

TYPICAL SWITCHING CHARACTERISTICS

TEST CIRCUIT 1




TEST CIRCUIT 2



OUTLINE DIMENSIONS

16-Lead Plastic Dual In-Line Package [PDIP] (N-16)


Dimensions shown in inches and (millimeters)



COMPLIANT TO JEDEC STANDARDS MO-095AC
CONTROLLING DIMENSIONS ARE IN INCHES; MILLIMETER DIMENSIONS (IN PARENTHESES) ARE ROUNDED-OFF INCH EQUIVALENTS FOR REFERENCE ONLY AND ARE NOT APPROPRIATE FOR USE IN DESIGN

16-Lead Ceramic Dual In-Line Package [CERDIP] (Q-16)


Dimensions shown in inches and (millimeters)



CONTROLLING DIMENSIONS ARE IN INCHES; MILLIMETERS DIMENSIONS (IN PARENTHESES) ARE ROUNDED-OFF INCH EQUIVALENTS FOR REFERENCE ONLY AND ARE NOT APPROPRIATE FOR USE IN DESIGN

20-Terminal Ceramic Leadless Chip Carrier [LCC] (E-20A)

Dimensions shown in inches and (millimeters)



CONTROLLING DIMENSIONS ARE IN INCHES; MILLIMETERS DIMENSIONS (IN PARENTHESES) ARE ROUNDED-OFF INCH EQUIVALENTS FOR REFERENCE ONLY AND ARE NOT APPROPRIATE FOR USE IN DESIGN