


THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
		P	LTR	DATE	DWN APVD
GP	00		B	REVISED PER ECO-08-007327	02OCT08 BM WM



1. THE CONTACT SURFACES OF THE TERMINALS ARE COATED WITH LUBRICANT.
2. ALL DIMENSIONS ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
3. MATERIAL:
HOUSING, COVER, AND CABLE CLAMP: POLYPHENYLENE OXIDE GRAY.
TERMINAL: PHOSPHOROUS BRONZE PLATED WITH .000030 [0.76μm] MIN GOLD OR GOLD FLASH OVER PALLADIUM NICKEL PLATE, .000030[0.76μm] MIN TOTAL ON MATING SURFACE. .000050[1.27μm] MIN NICKEL UNDERPLATE OVER ENTIRE TERMINAL.
4. COVER, SCREW & CABLE CLAMP SHIPPED UNASSEMBLED.
5. WIRE SIZE: 24-26 AWG SOLID OR 24 AWG STRANDED COPPER CONDUCTORS, MAXIMUM INSULATION DIAMETER OF .045[1.15] IS ACCEPTABLE FOR MOST APPLICATIONS.
6. CABLE RANGE: .425[10.80] DIAMETER MAX.
7. 500 KITS BULK PACKAGED.
8. CORING IS AN OPTIONAL CONFIGURATION AND IS AT THE DISCRETION OF AMP.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. MCMASTER	27OCT05	Tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608			
		CHK W. MILLHIMES	27OCT05				
DIMENSIONS: INCHES [mm]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME PLUG KIT, 50 POSITION, B-SLOT, WITH 90 DEGREE COVER AND SCREW, CHAMP-LOK			
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC			
				APPLICATION SPEC			
MATERIAL		FINISH		WEIGHT	SIZE A2	CAGE CODE 00779	DRAWING NO C=5556821
3		3		CUSTOMER DRAWING	SCALE 2:1	SHEET 1 of 1	RESTRICTED TO REV B