
Part Number : 347920081
Product Description : Mini50 Unsealed Vertical Header, UL 94 HB, Single Row, 8 Circuit, Polarization Option B, Gray, Tray
Series Number : 34792
Status : Active
Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

347920081_sd.pdf

PK-31301-440-001.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

Specifications

AS-34791-020-CH-001.pdf

2065230000-AS-000.pdf

AS-34791-020-001.pdf

AS-34791-020-CH-001.pdf

AS-34791-020-FR-001.pdf

2065230000-AS-KR-000.pdf

PS-34791-020-001.pdf

2065230000-TS-000.pdf

347910020-TS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 33
China RoHS	

Downloaded from Arrow.com.

	per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	34792
Description	Mini50 Unsealed Vertical Header, UL 94 HB, Single Row, 8 Circuit, Polarization Option B, Gray, Tray
Application	Automotive, Wire-to-Board
Component Type	PCB Header
Product Name	Mini50
UPC	884982492868

Electrical

Current - Maximum per Contact	4.0A (for reference only)

Downloaded from Arrow.com.

Voltage - Maximum	14V (typical operating)

Physical

Breakaway	No
Circuits (Loaded)	8
Circuits (maximum)	8
Color - Resin	Gray
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester Alloy
Net Weight	1.600/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Tray
PCB Locator	Yes
PC Tail Length	2.90mm
Pitch - Mating Interface	2.00mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Through Hole

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mini50 Unsealed Receptacle Housings	34791
Mini50 Unsealed Dual Row	206523

Downloaded from Arrow.com.

Receptacles	

Downloaded from Arrow.com.