


COAXIAL CONNECTOR, SMC, 50 Ohm, Straight cable plug (male)

11_SMC-50-2-13/111_N

Properties

- Screw-on mechanism permits a vibration-proof connection
- Suitable for semi-permanent connections and for use in mobile equipment
- Applicable in frequencies up to 10 GHz



Product configuration		
Interface type	Gender	Standard
SMC	plug	IEC 60169-9_MIL-STD-348A/312_CECC 22140

Interface and material data		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Brass	Gold Plating (Nickel underplated)
Body	Brass	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	
Coupling nut	Brass	Gold Plating (Nickel underplated)

Electrical data	
Impedance	50 Ω
Interface frequency	10 GHz

Mechanical data	
Weight	0.0018 kg
Mating cycles	500
Cable entry centre contact	soldered
Cable entry outer contact	soldered

Environmental data	
Operation temperature	-65 °C ... 165 °C

COAXIAL CONNECTOR, SMC, 50 Ohm, Straight cable plug (male)
11_SMC-50-2-13/111_N

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22650675	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
22650675	11_SMC-50-2-13/111_NH	Bulk 100 pcs

Suitable cables	
Cable group	Y3 - 2 mm / 50 Ohm
	Y11 - 2 mm / 50 Ohm
Suitable cables	SR_86_TP_M17

Additional Information	
Only as assembly	No

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P3415 / Date of publication: 12.07.2025 / uncontrolled copy