
Part Number : 1200680211
Product Description : M12 Signal, A-Coded, In-Line Splitter, 1 x 4 Poles Male (Straight) to 2 x 3 Poles Female (Straight), 0.34mm² (22 AWG), TPE Cable, 0.30m (0.99') Length
Series Number : 120068
Status : Active
Product Category : Industrial Tees and Splitters
Engineering Part Number : 884A31K05M003



Documents and Resources

Drawings

1200680211_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

Downloaded from Arrow.com.

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Industrial Tees and Splitters
Series	120068
Description	M12 Signal, A-Coded, In-Line Splitter, 1 x 4 Poles Male (Straight) to 2 x 3 Poles Female (Straight), 0.34mm² (22 AWG), TPE Cable, 0.30m (0.99') Length
IP Rating	IP67
Product Name	M12 Signal,Micro-Change (M12)
Type	Splitter - In-line
UPC	78678883476

Agency

CSA	LR6837
UL	E152210

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

Physical

Color - Cable Jacket	Yellow
Drop Connector	Micro-Change (M12)
Drop Gender	Male
Keyway	Single
LED Indicator	None
Left Trunk Connector	Micro-Change (M12)

Downloaded from Arrow.com.

Left Trunk Gender	Female
Leg 1 Length	0.30m
Leg 2 Length	0.30m
Material - Cable Jacket	TPE
Material - Connector Body	TPE
Material - Coupling Nut	Nickel-plated Brass
Net Weight	100.073/g
Poles	3 Female/4 Male
Right Trunk Connector	Micro-Change (M12)
Right Trunk Gender	Female
Temperature Range - Operating	-30° to +70°C

Downloaded from Arrow.com.