Final datasheet

XHP™3 module with Trench/Fieldstop IGBT3 and emitter controlled 3 diode

Features



- Electrical features
  - V_{CES} = 3300 V
  - $I_{C\ nom}$ = 450 A / I_{CRM} = 900 A
  - Low switching losses
  - High DC stability
  - High short-circuit capability
  - Low $V_{CE,sat}$
  - $T_{vj,op}$ = 150°C
  - Unbeatable robustness
  - $V_{CE,sat}$ with positive temperature coefficient
- Mechanical features
  - AlSiC base plate for increased thermal cycling capability
  - Isolated base plate
  - Package with CTI > 600


Potential applications

- Medium-voltage converters
- Motor drives
- Traction drives
- UPS systems
- Wind turbines

Product validation

- Qualified for industrial applications according to the relevant tests of IEC 60747, 60749 and 60068

Description



Downloaded from Arrow.com.

Table of contents

Description . . . 1
Features . . . 1
Potential applications . . . 1
Product validation . . . 1
Table of contents . . . 2
1 Package . . . 3
2 IGBT, Inverter . . . 3
3 Diode, Inverter . . . 5
4 Characteristics diagrams . . . 7
5 Circuit diagram . . . 11
6 Package outlines . . . 12
7 Module label code . . . 13
Revision history . . . 14
Disclaimer . . . 15

Downloaded from Arrow.com.

1 Package

Table 1 Insulation coordination

Parameter	Symbol	Note or test condition	Values	Unit
Isolation test voltage	V_{ISOL}	RMS, f = 50 Hz, *t* = 60 s	6.0	kV
Partial discharge extinction voltage	V_{isol}	RMS, f = 50 Hz, Q_{PD} ≤ 10 pC	2.6	kV
Material of module baseplate			AlSiC	
Comparative tracking index	*CTI*		> 600	

Table 2 Characteristic values

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Stray inductance module	L_{sCE}				25		nH
Module lead resistance, terminals - chip	$R_{AA'+CC'}$	T_C = 25 °C, per switch			0.31		mΩ
Module lead resistance, terminals - chip	$R_{CC'+EE'}$	T_C = 25 °C, per switch			0.41		mΩ
Storage temperature	T_{stg}			-40		150	°C
Mounting torque for module mounting	*M*	- Mounting according to valid application note	M6, Screw	4.25		5.75	Nm
Terminal connection torque	*M*	- Mounting according to valid application note	M3, Screw	0.9		1.1	Nm
			M8, Screw	8		10	
Weight	*G*				700		g

2 IGBT, Inverter

Table 3 Maximum rated values

Parameter	Symbol	Note or test condition		Values	Unit
Collector-emitter voltage	V_{CES}		T_{vj} = -40 °C	3300	V
			T_{vj} = 150 °C	3300	
Continuous DC collector current	I_{CDC}	$T_{vj\,max}$ = 150 °C	T_C = 100 °C	450	A
Repetitive peak collector current	I_{CRM}	t_p limited by $T_{vj\,op}$		900	A
Gate-emitter peak voltage	V_{GES}			±20	V

Downloaded from Arrow.com.

Table 4 Characteristic values

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Collector-emitter saturation voltage	$V_{CE\,sat}$	I_C = 450 A, V_{GE} = 15 V	T_{vj} = 25 °C		2.50	2.75	V
			T_{vj} = 125 °C		2.90		
			T_{vj} = 150 °C		3.00	3.30	
Gate threshold voltage	V_{GEth}	I_C = 21 mA, V_{CE} = V_{GE}, T_{vj} = 25 °C		5.20	5.80	6.40	V
Gate charge	Q_G	V_{GE} = ±15 V, V_{CC} = 1800 V, T_{vj} = 25 °C			12.5		µC
Internal gate resistor	R_{Gint}	T_{vj} = 25 °C			1.3		Ω
Input capacitance	C_{ies}	f = 1000 kHz, T_{vj} = 25 °C, V_{CE} = 25 V, V_{GE} = 0 V			84		nF
Reverse transfer capacitance	C_{res}	f = 1000 kHz, T_{vj} = 25 °C, V_{CE} = 25 V, V_{GE} = 0 V			2		nF
Collector-emitter cut-off current	I_{CES}	V_{CE} = 3300 V, V_{GE} = 0 V	T_{vj} = 25 °C			5	mA
Gate-emitter leakage current	I_{GES}	V_{CE} = 0 V, V_{GE} = 20 V, T_{vj} = 25 °C				400	nA
Turn-on delay time (inductive load)	t_{don}	I_C = 450 A, V_{CC} = 1800 V, V_{GE} = ±15 V, R_{Gon} = 0.7 Ω	T_{vj} = 25 °C		0.530		µs
			T_{vj} = 125 °C		0.570		
			T_{vj} = 150 °C		0.580		
Rise time (inductive load)	t_r	I_C = 450 A, V_{CC} = 1800 V, V_{GE} = ±15 V, R_{Gon} = 0.7 Ω	T_{vj} = 25 °C		0.100		µs
			T_{vj} = 125 °C		0.130		
			T_{vj} = 150 °C		0.130		
Turn-off delay time (inductive load)	t_{doff}	I_C = 450 A, V_{CC} = 1800 V, V_{GE} = ±15 V, R_{Goff} = 3.3 Ω	T_{vj} = 25 °C		1.710		µs
			T_{vj} = 125 °C		1.860		
			T_{vj} = 150 °C		1.920		
Fall time (inductive load)	t_f	I_C = 450 A, V_{CC} = 1800 V, V_{GE} = ±15 V, R_{Goff} = 3.3 Ω	T_{vj} = 25 °C		0.130		µs
			T_{vj} = 125 °C		0.240		
			T_{vj} = 150 °C		0.270		
Turn-on time (resistive load)	t_{on_R}	I_C = 500 A, V_{CC} = 2000 V, V_{GE} = ±15 V, R_{Gon} = 0.7 Ω	T_{vj} = 25 °C	1.15			µs
Turn-on energy loss per pulse	E_{on}	I_C = 450 A, V_{CC} = 1800 V, L_σ = 85 nH, V_{GE} = ±15 V, R_{Gon} = 0.7 Ω, di/dt = 3650 A/µs (T_{vj} = 150 °C)	T_{vj} = 25 °C		500		mJ
			T_{vj} = 125 °C		765		
			T_{vj} = 150 °C		845		
Turn-off energy loss per pulse	E_{off}	I_C = 450 A, V_{CC} = 1800 V, L_σ = 85 nH, V_{GE} = ±15 V, R_{Goff} = 3.3 Ω, dv/dt = 2850 V/µs (T_{vj} = 150 °C)	T_{vj} = 25 °C		415		mJ
			T_{vj} = 125 °C		610		
			T_{vj} = 150 °C		670		

(table continues...)

Downloaded from Arrow.com.

Table 4 (continued) Characteristic values

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
SC data	I_{SC}	$V_{GE} \leq 15$ V, $V_{CC} = 2500$ V, $V_{CEmax}=V_{CES}-L_{sCE}*di/dt$	$t_P \leq 10$ µs, $T_{vj} \leq 150$ °C		1800		A
Thermal resistance, junction to case	R_{thJC}	per IGBT				28.4	K/kW
Thermal resistance, case to heat sink	R_{thCH}	per IGBT, $\lambda_{grease} = 1$ W/(m·K)			17.4		K/kW
Temperature under switching conditions	$T_{vj\,op}$			-40		150	°C

3 Diode, Inverter

Table 5 Maximum rated values

Parameter	Symbol	Note or test condition		Values	Unit
Repetitive peak reverse voltage	V_{RRM}		$T_{vj} = -40$ °C	3300	V
			$T_{vj} = 150$ °C	3300	
Continuous DC forward current	I_F			450	A
Repetitive peak forward current	I_{FRM}	$t_P = 1$ ms		900	A
I^2t - value	I^2t	$t_P = 10$ ms, $V_R = 0$ V	$T_{vj} = 125$ °C	82.9	kA^2s
			$T_{vj} = 150$ °C	68	
Maximum power dissipation	P_{RQM}		$T_{vj} = 150$ °C	1000	kW
Minimum turn-on time	t_{onmin}			10	µs

Table 6 Characteristic values

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Forward voltage	V_F	$I_F = 450$ A, $V_{GE} = 0$ V	$T_{vj} = 25$ °C		3.10	3.50	V
			$T_{vj} = 125$ °C		2.75		
			$T_{vj} = 150$ °C		2.65	2.95	
Peak reverse recovery current	I_{RM}	$V_{CC} = 1800$ V, $I_F = 450$ A, $V_{GE} = -15$ V, $-di_F/dt = 3650$ A/µs ($T_{vj} = 150$ °C)	$T_{vj} = 25$ °C		680		A
			$T_{vj} = 125$ °C		680		
			$T_{vj} = 150$ °C		680		

(table continues...)

Downloaded from Arrow.com.

Table 6 (continued) Characteristic values

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Recovered charge	Q_r	V_{CC} = 1800 V, I_F = 450 A, V_{GE} = -15 V, -di$_F$/dt = 3650 A/µs (T_{vj} = 150 °C)	T_{vj} = 25 °C		230		µC
			T_{vj} = 125 °C		445		
			T_{vj} = 150 °C		525		
Reverse recovery energy	E_{rec}	V_{CC} = 1800 V, I_F = 450 A, V_{GE} = -15 V, -di$_F$/dt = 3650 A/µs (T_{vj} = 150 °C)	T_{vj} = 25 °C		220		mJ
			T_{vj} = 125 °C		490		
			T_{vj} = 150 °C		595		
Thermal resistance, junction to case	R_{thJC}	per diode				45.5	K/kW
Thermal resistance, case to heat sink	R_{thCH}	per diode, λ_{grease} = 1 W/(m·K)			19.3		K/kW
Temperature under switching conditions	$T_{vj\,op}$			-40		150	°C


Downloaded from Arrow.com.

4 Characteristics diagrams

Output characteristic (typical), IGBT, Inverter

$I_C = f(V_{CE})$


V_{GE} = 15 V



Output characteristic field (typical), IGBT, Inverter

$I_C = f(V_{CE})$


T_{vj} = 150 °C



Transfer characteristic (typical), IGBT, Inverter

$I_C = f(V_{GE})$


V_{CE} = 20 V



Gate charge characteristic (typical), IGBT, Inverter

$V_{GE} = f(Q_G)$

I_C = 450 A, T_{vj} = 25 °C




Downloaded from Arrow.com.

Capacity characteristic (typical), IGBT, Inverter

$C = f(V_{CE})$


$f = 1000$ kHz, $V_{GE} = 0$ V, $T_{vj} = 25$ °C



Switching times (typical), IGBT, Inverter

$t = f(I_C)$


$R_{Goff} = 3.3\ \Omega$, $R_{Gon} = 0.7\ \Omega$, $V_{GE} = \pm 15$ V, $V_{CC} = 1800$ V, $T_{vj} = 150$ °C



Switching times (typical), IGBT, Inverter

$t = f(R_G)$


$V_{GE} = \pm 15$ V, $I_C = 450$ A, $V_{CC} = 1800$ V, $T_{vj} = 150$ °C



Switching losses (typical), IGBT, Inverter

$E = f(I_C)$

$R_{Goff} = 3.3\ \Omega$, $R_{Gon} = 0.7\ \Omega$, $V_{GE} = \pm 15$ V, $V_{CC} = 1800$ V




Downloaded from Arrow.com.

Switching losses (typical), IGBT, Inverter

$E = f(R_G)$


$V_{GE} = \pm 15$ V, $I_C = 450$ A, $V_{CC} = 1800$ V



Reverse bias safe operating area (RBSOA), IGBT, Inverter


$I_C = f(V_{CE})$

$R_{Goff} = 3.3\ \Omega$, $V_{GE} = \pm 15$ V, $T_{vj} = 150$ °C




Transient thermal impedance, IGBT, Inverter

$Z_{th} = f(t)$



Forward characteristic (typical), Diode, Inverter

$I_F = f(V_F)$




Downloaded from Arrow.com.

Switching losses (typical), Diode, Inverter

$E_{rec} = f(I_F)$


V_{CE} = 1800 V, $R_{Gon} = R_{Gon}$(IGBT)



Switching losses (typical), Diode, Inverter

$E_{rec} = f(R_G)$


V_{CE} = 1800 V, I_F = 450 A



Safe operating area (SOA), Diode, Inverter


$I_R = f(V_R)$

T_{vj} = 150 °C



Transient thermal impedance, Diode, Inverter

$Z_{th} = f(t)$



Downloaded from Arrow.com.

5 Circuit diagram




Figure 1

Downloaded from Arrow.com.

6 Package outlines




Figure 2

Downloaded from Arrow.com.

7 Module label code


Module label code			
Code format	Data Matrix		Barcode Code128
Encoding	ASCII text		Code Set A
Symbol size	16x16		23 digits
Standard	IEC24720 and IEC16022		IEC8859-1
Code content	*Content* Module serial number Module material number Production order number Date code (production year) Date code (production week)	*Digit* 1 – 5 6 - 11 12 - 19 20 – 21 22 – 23	*Example* 71549 142846 55054991 15 30
Example	 7154914284655054991530	 7154914284655054991530	

Figure 3

Downloaded from Arrow.com.

Revision history

Document revision	Date of release	Description of changes
V1.0	2013-12-05	Target datasheet
V1.1	2014-08-25	Target datasheet
V1.2	2015-01-22	Target datasheet
V1.3	2015-10-16	Target datasheet
V1.4	2015-10-16	Target datasheet
V2.0	2016-05-18	Preliminary datasheet
V2.1	2016-09-02	Preliminary datasheet
V2.2	2016-12-23	Preliminary datasheet
V2.3	2018-02-14	Preliminary datasheet
V3.0	2018-12-12	Final datasheet
V3.1	2018-12-13	Final datasheet
V3.2	2020-01-27	Final datasheet
n/a	2020-09-01	Datasheet migrated to a new system with a new layout and new revision number schema: target or preliminary datasheet = 0.xy; final datasheet = 1.xy
1.10	2021-11-04	Final datasheet
1.20	2022-04-06	Final datasheet
1.30	2026-04-01	Typo correction for Ic condition at Vgeth and harmonization of insulation coordination information

Downloaded from Arrow.com.

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2026-04-01

Published by

Infineon Technologies AG

81726 Munich, Germany

© 2026 Infineon Technologies AG

All Rights Reserved.

Do you have a question about any aspect of this document?

Email: erratum@infineon.com

Document reference
IFX-AAX244-015

Important notice

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

Warnings

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.

Downloaded from Arrow.com.