






| REVISIONS |                                  |           |        |
|-----------|----------------------------------|-----------|--------|
| REV       | DESCRIPTION, ECN, EAR NO.        | DATE      | APP'D  |
| A         | PROPOSAL PER ECN E07035          | FEB 27/07 | L.CHAN |
| J         | PROPOSAL                         | JAN 30/08 | L.CHAN |
| K         | ADD TIN DIPPED ON SHIELD TAIL    | SEP 20/12 | L.CHAN |
| L         | ADD PIN DIMENSIONS AND TOLERANCE | FEB 15/17 | L.CHAN |



AMPHENOL PART NUMBER: RJULE-4X182-01



CONTACT PLATING CODE  
 0 = GOLD FLASH  
 1 = 15u"  
 2 = 30u"  
 3 = 50u"

#### NOTES:

#### MATERIALS:

HOUSING: HIGH TEMPERATURE THERMOPLASTIC.  
 FLAMMABILITY RATING UL 94V-0  
 COLOUR: BLACK  
 CONTACTS: PHOSPHOR BRONZE  
 PLATING: GOLD PLATING ON MATING SURFACES.  
 SEE PART NUMBER SYSTEM OPTION  
 50 u" [1.27 MICRONS] MIN. NICKEL UNDERPLATE.  
 100 u" [2.54 MICRONS] MIN. MATTE TIN ON  
 SOLDER AREA.

SHELL: BRASS  
 NICKEL PLATING WITH TIN DIPPED ON PCB TAIL.



|                            |            |                        |           |      |           |
|----------------------------|------------|------------------------|-----------|------|-----------|
| UNLESS SPECIFIED OTHERWISE |            | DRAWN                  | Jack Wang | DATE | FEB 27/07 |
| PRIMARY UNITS              | MILLIMETER | CHECKED                | MT.Chen   | DATE | FEB 27/07 |
| SECONDARY                  | INCH       | M.E. APP'D             | YM Lee    | DATE | FEB 27/07 |
| REFERENCE IN PARENTHESES   |            | Q.A. APP'D             |           |      |           |
| GENERAL TOLERANCES         |            | DWG APPR.              |           |      |           |
| 1 DECIMAL PLACE            |            | ENG. REL. NO.          |           |      |           |
| 2 DECIMAL PLACES           |            | REF.                   |           |      |           |
| 3 DECIMAL PLACES           |            | THIRD ANGLE PROJECTION |           |      |           |
| ANGULAR DEGREES            |            | DO NOT SCALE DRAWING   |           |      |           |

|                       |  |                                                                                                                                      |
|-----------------------|--|--------------------------------------------------------------------------------------------------------------------------------------|
| Amphenol Canada Corp. |  | www.amphenolcanada.com                                                                                                               |
| TITLE                 |  | RJ ULTRA LOW PROFILE MODULAR JACK<br>8 POSITIONS, 8 CONTACTS, SHIELD<br>WITH REAR PANEL MOUNT TABS.<br>WITHOUT FLANGE-RoHS COMPLIANT |
| DWG. NO.              |  | P- RJULE-4X182-01                                                                                                                    |
| CODE ID NO. 03554     |  | DWG SIZE: C SCALE: N/A SHEET 1 OF 1                                                                                                  |