



Color: ■ white

Dimensions in mm
Plate thickness: 0.5 ... 2 mm Cutout tolerance: + 0.1 mm Please note!

Cover WINSTA® MINI 2-pole

The cover from the WINSTA® MINI product line guarantees you the maximum flexibility in electrical installation. You can rely on the quality of WINSTA® components from WAGO for your electrical installation accessories too. WINSTA® MINI follows the trend towards miniaturisation. Our smallest pluggable connection system is especially suitable for lights, for instance, since as a result of LED technology; due to complex systems, these offer much less space for the connection technology.

Lower costs through fast commissioning and elimination of service expenses – solutions from WINSTA® MINI

The WINSTA® Pluggable Connection System is ideally tailored to the strict requirements of building installation. It makes electrical installation pluggable, and thus faster, more reliable, and error-free. Use of this pre-assembled system decreases assembly times and installation errors at the construction site. Enjoy the benefits of the pluggable version of our maintenance-free spring pressure connection technology too! Plan your installation with with protection against mismatch from WAGO.

- compact design for conductors with a cross-section up to 1.5 mm²
- rapid, structured electrical installation

Notes

General safety information

NOTICE: Observe installation and safety instructions!

1. Only to be used by a qualified electrician or by a person electrically instructed for the task (EIP per DIN VDE 0105-100).
 2. Do not install while energized or under load.
 3. Use only for its intended purpose.
 4. Observe applicable national regulations, standards and directives.
 5. Observe the technical specifications of the products.
 6. Ensure correct polarity assignment.
 7. Do not use damaged or contaminated components.
 8. Observe conductor types, conductor cross-sections, strip lengths and cable diameters.
 9. Insert conductors up to the stop.
 10. Use only with locking lever and strain relief.
 11. Use original accessories only.
- To be sold only with installation instructions!**

Note

The snap-in connectors must be relieved of tensile and transverse forces. A surface finish can influence the edge radius of the cutouts. This may affect the snap-in socket fit, so ensure an adequate fit before use. In addition, the punched edge should be on the inside for punched cutouts. The wings of the snap-in connectors must not be mechanically stressed for a long period before use (e.g., due to a pre-locking position).

Connection Data

Connection 1

Pole number	2
-------------	---

Physical data

Width	21.6 mm / 0.85 inches
Height	16 mm / 0.63 inches
Depth	10.1 mm / 0.398 inches

Mechanical data

Mounting type	Snap-in flange
Suitable	for cutout

Material data

Note (material data)	Information on material specifications can be found here
Color	white
Insulation material (main housing)	Polyamide (PA66)
Flammability class per UL94	V0
Fire load	0.033 MJ
Weight	1.2 g

Environmental requirements

Processing temperature	-5 ... +40 °C
Continuous operating temperature	-35 ... +85 °C
Note on continuous operating temperature	Insulating parts for temperatures ≤ 105 °C

Commercial data

Product Group	20 (Winsta)
PU (SPU)	100 pcs
Packaging type	Box
Country of origin	DE
GTIN	4045454526504
Customs tariff number	39269097900

Product Classification

UNSPSC	39121721
eCl@ss 10.0	27-44-06-92
eCl@ss 9.0	27-44-06-92
ETIM 9.0	EC002863
ETIM 10.0	EC002863
ECCN	NO US CLASSIFICATION

Environmental Product Compliance

RoHS Compliance Status	Compliant, No Exemption
------------------------	-------------------------

Downloads

Environmental Product Compliance

Compliance Search	
Environmental Product Compliance 890-692	↓

Documentation

Bid Text			
890-692	19.02.2019	xml 2.56 KB	↓
890-692	20.11.2014	doc 22.50 KB	↓

CAD/CAE-Data

CAD data	
2D/3D Models 890-692	↓

CAE data	
WSCAD Universe 890-692	↓
ZUKEN Portal 890-692	↓

Subject to changes. Please also observe the further product documentation!

Current addresses can be found at: www.wago.com