Part Number : 1210360577
Product Description : Brad mPm DIN Dual Form A-18mm to Micro-Change (M12) 5 Pole Cordset, C4 Circuit, Yellow LED, Dual Male (90°) to Male (Straight), 0.50mm² Black PUR Cable, 1.0m (3.28') Length, 24V
Series Number : 121036
Status : Active
Product Category : Industrial Cable Assemblies
Engineering Part Number : E85AB0P12M010



Documents and Resources

Drawings

1210360577_sd.pdf

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Downloaded from Arrow.com.

Part Details

General

Status	Active
Category	Industrial Cable Assemblies
Series	121036
Description	Brad mPm DIN Dual Form A-18mm to Micro-Change (M12) 5 Pole Cordset, C4 Circuit, Yellow LED, Dual Male (90°) to Male (Straight), 0.50mm² Black PUR Cable, 1.0m (3.28') Length, 24V
IP Rating	IP65
Product Name	Micro-Change (M12),mPm
Protocol	N/A
Type	Double Ended
UPC	883906335038

Electrical

Current - Maximum per Contact	Contact Molex
Voltage - Maximum	24V

Physical

Cable Diameter	5.50mm (.216")
Cable Length	1.0m (3.28')
Color - Cable Jacket	Black
Connector End A	Brad mPm DIN A - 18mm
Connector End B	Micro-Change (M12)
Coupling Style	Threaded
Gender	Male-Male
Keyway	Single
LED Indicator	Yellow
Material - Cable Jacket	PUR
Material - Connector Body	Polypropylene
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold

Downloaded from Arrow.com.

Net Weight	174.950/g
Orientation	90°/90° to Straight
Poles	5
Temperature Range - Operating	-25° to +75°C
Wire/Cable Type	PUR
Wire Size (AWG)	20

Downloaded from Arrow.com.