

Inductors

For Power Line SMD

NLC Series NLC5650 Type

FEATURES

- The NLC series feature low DC resistance and high current handling capacities, making them ideal for power supply line applications.
- They are available in ranging from 2520 to 5650 types.

APPLICATIONS


Portable telephones, personal computers, hard disk drives, and other electronic equipment.

SPECIFICATIONS


Operating temperature range	-20 to +85°C
Storage temperature range	-40 to +85°C [Unit of products]

RECOMMENDED SOLDERING CONDITIONS

REFLOW SOLDERING




FLOW SOLDERING



IRON SOLDERING

Perform soldering at 250°C on 30W max. within 5 seconds.

VAPOR-PHASING



FLUX AND CLEANING

Rosin-based flux is recommended.

Cleaning Conditions

Solvent	Please select the solvent of this product avoiding a strong acid and a strong alkali, and considering the environments.
Time	2min max.

PRODUCT IDENTIFICATION

NLC 565050 T- 2R2 K
(1) (2) (3) (4) (5)

(1) Series name

(2) Dimensions L×W×T

565050 5.6×5.0×5.0mm

(3) Packaging style

T Taping(reel)

(4) Inductance value

1R0 1μH
330 33μH

(5) Inductance tolerance

K ±10%

PACKAGING STYLE AND QUANTITIES



Packaging style	Quantity
Taping	400 pieces/reel

Inductors

For Power Line SMD

NLC Series NLC5650 Type

SHAPES AND DIMENSIONS/RECOMMENDED PC BOARD PATTERN



Dimensions in mm

ELECTRICAL CHARACTERISTICS

Inductance (μ H)	Inductance tolerance	Q min.	Test frequency L, Q (MHz)	Self-resonant frequency (MHz)min.	DC resistance (Ω)max.	Rated current (mA)max.	Part No.
1	±10%	10	7.96	95	0.03	1800	NLC565050T-1R0K
1.2	±10%	10	7.96	70	0.035	1700	NLC565050T-1R2K
1.5	±10%	10	7.96	55	0.04	1600	NLC565050T-1R5K
1.8	±10%	10	7.96	47	0.05	1400	NLC565050T-1R8K
2.2	±10%	10	7.96	42	0.06	1300	NLC565050T-2R2K
2.7	±10%	10	7.96	37	0.07	1200	NLC565050T-2R7K
3.3	±10%	10	7.96	34	0.08	1120	NLC565050T-3R3K
3.9	±10%	10	7.96	32	0.09	1050	NLC565050T-3R9K
4.7	±10%	10	7.96	29	0.11	950	NLC565050T-4R7K
5.6	±10%	10	7.96	26	0.13	880	NLC565050T-5R6K
6.8	±10%	10	7.96	24	0.15	810	NLC565050T-6R8K
8.2	±10%	10	7.96	22	0.18	750	NLC565050T-8R2K
10	±10%	10	2.52	19	0.21	690	NLC565050T-100K
12	±10%	10	2.52	17	0.25	630	NLC565050T-120K
15	±10%	10	2.52	16	0.3	580	NLC565050T-150K
18	±10%	10	2.52	14	0.36	530	NLC565050T-180K
22	±10%	10	2.52	13	0.43	480	NLC565050T-220K
27	±10%	10	2.52	11.5	0.52	440	NLC565050T-270K
33	±10%	10	2.52	10.5	0.62	400	NLC565050T-330K
39	±10%	10	2.52	9.5	0.72	370	NLC565050T-390K
47	±10%	10	2.52	8.5	0.85	340	NLC565050T-470K
56	±10%	10	2.52	7.8	1	310	NLC565050T-560K
68	±10%	10	2.52	7	1.2	290	NLC565050T-680K
82	±10%	10	2.52	6.4	1.4	270	NLC565050T-820K
100	±10%	20	0.796	6	1.6	250	NLC565050T-101K
120	±10%	20	0.796	5.4	1.9	230	NLC565050T-121K
150	±10%	20	0.796	4.8	2.2	210	NLC565050T-151K
180	±10%	20	0.796	4.4	2.8	190	NLC565050T-181K
220	±10%	20	0.796	3.9	3.4	170	NLC565050T-221K
270	±10%	20	0.796	3.6	4.2	155	NLC565050T-271K
330	±10%	20	0.796	3.2	4.9	140	NLC565050T-331K
390	±10%	20	0.796	2.9	5.8	130	NLC565050T-391K
470	±10%	20	0.796	2.6	7	120	NLC565050T-471K
560	±10%	20	0.796	2.4	8.5	110	NLC565050T-561K
680	±10%	20	0.796	2.2	10	100	NLC565050T-681K
820	±10%	20	0.796	2	13	90	NLC565050T-821K
1000	±10%	20	0.252	1.8	15	85	NLC565050T-102K

- Test equipment L, Q: YHP4194A IMPEDANCE ANALYZER+YHP16085A+YHP16093B+TF-1, or equivalent
- SRF: HP8753C NETWORK ANALYZER ($Z_{in}=Z_{out}=50\Omega$), or equivalent
- Rdc: MATSUSHITA VP-2941A DIGITAL MILLIOHM METER, or equivalent


• All specifications are subject to change without notice.

Inductors

For Power Line
SMD

NLC Series NLC5650 Type

TYPICAL ELECTRICAL CHARACTERISTICS INDUCTANCE CHANGE vs. DC SUPERPOSITION CHARACTERISTICS



- All specifications are subject to change without notice.