

**MICRO SWITCH**FREEPORT, ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL

FED. MFG. CODE 91929

SWITCH - BASIC

CATALOG LISTING

BZ-2RL224CATALOG LISTING
BZ-2RL224
PAGE 1 OF 1**M**DRAWING
NUMBER

7

ISSUE

REPLACES

RELEASE NO.

CHECK

REVISIONS

A C017410

G C H
27 APR 63B C0-
75204BK D R
1 FEB 94C C0-
77591DAW
27 JUN 94

D C093346

DLT
9 SEP 98E C0-
94212-EDCS
7 SEP 99

F 204582

CSL
14 DEC 01

CHECK

63

22 MAY 63

L.S.D

CHECK

63

27 APR 63

DRAWN

G C H


27 APR 63

CHECK

63

RASTER

FO-50378



NOTES

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .139 MAX DIA ON 1.000 ± .002 CENTERS
2 - SWITCH WILL WITHSTAND TEMPERATURE OF 250° F

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL
OPERATING FORCE ----- 5 OZ MAX	CONTACT ARRANGEMENT S P D T	DO NOT SCALE PRINT
RELEASE FORCE ----- 1/2 OZ MIN	UNDERWRITERS' LAB. INC. LISTED RATING	UNLESS OTHERWISE NOTED
DIFFERENTIAL TRAVEL ----- .050 MAX	-L96- 15 A-125, 250, OR 480 VAC	DIMENSIONS ARE IN INCHES
DO NOT OVERTRAVEL MORE THAN ----- .060	1/2 A-125 VDC, 1/4 A-250 VDC	TOLERANCES ARE:
	1/8 HP-125 VAC, 1/4 HP-250 VAC	ONE PLACE (.0) ±.030
	-L288- CE D SP	TWO PLACE (.00) ±.015
	-L299- 16A 250V T85 5E4	THREE PLACE (.000) ±.005
	-L306-	ANGLES ±
		WEIGHT .060 LB