





Characteristics



C146 D
für gestanzte Crimpkontakte
for stamped crimp contacts

Alle technischen Daten wurden unter Laborbedingungen ermittelt und können im Praxisbetrieb abweichen.
Es handelt sich bei den Angaben weder um Beschaffenheits- noch um Haltbarkeitsgarantien.
All technical data have been measured in a laboratory environment and can be different during practical usage of the product. Any product information is for descriptive usage only and not legally binding; particularly the information does not constitute or provide any legal guarantees ("Beschaffenheitsgarantie" or "Haltbarkeitsgarantie").

General Characteristics	Standard	Value
number of contacts		40
termination technique		crimp
wire gauge		0,14 mm ² - 2,5 mm ² AWG 26 - AWG 14
max. insulation diameter		4,3 mm
flammability	UL 94	V-0
Electrical Characteristics	Standard	Value
rated voltage	IEC 60664-1	250 V
pollution degree	IEC 60664-1	3
installation (overvoltage) category	IEC 60664-1	3
material group	IEC 60664-1	3a
rated impulse withstand voltage	IEC 60664-1	4 kV
rated current T _{amb} = 40 °C		10 A
current carrying capacity	IEC 60512-5-2	see derating curve
contact resistance	IEC 60512-2-1	≤ 5 mΩ
insulation resistance	IEC 60512-3-1	≥ 10 ¹⁰ Ω
Climatical Characteristics	Standard	Value
climatic category	IEC 60068-1	40 / 125 / 21
upper temperature	IEC 60512-11-9	+125 °C
lower temperature	IEC 60512-11-10	-40 °C
Mechanical Characteristics	Standard	Value
mechanical operation	IEC 60512-9-1	≥500 mating cycles
Materials	Standard	Value
insert		PC GF grey
contacts		CuZn (brass)
contact plating		Ag (silver)/Au (gold)

Gewicht (errechnet) / Calc WT: 62,4 g				Zul. Abw./Tolerances:		Maßstab / Scale: 1:1 (1:2)		A3				
Prüfmaß / Testdimension						DIN / ISO 13715		CUSTOMER DRAWING				
Teileindex / Partindexnumber:												
Bagatelle change:												
				Gez.	11.12.2013	Buchseneinsatz 40pol <i>female insert 40pole</i>						
				Drawn	jhoennige							
				Status	Released							
				Gepr.	09.05.2017							
				Checked	MGRIMM							
05	201700173	24.04.2017	IMOHR	Amphenol Tuchel Industrial GmbH		M	C146 10B040 000 2				Blatt / Sheet 1	
04	201500911	05.02.2016	JHÖNN								1 Bl.	
Index	Änderung / Description		Datum / Date	Name	Ers. f. / Replacement for: M-C146 10B040 000 2 Rev03							