Part Number : 1202530623
Product Description : Contrinex Inductive Sensor, C23 (20 x 32mm) Fully Stainless Steel, 7mm Operating Distance, Embeddable, PNP, NO, 0.2m 3-wire PVC Cable, 3-pin M8 Connector
Series Number : 120253
Status : Not Recommended For New Design
Product Category : Inductive and Photoelectric Sensors
Engineering Part Number : DW-AV-703-C23-276



Documents and Resources

Specifications

1202530617-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per D(2022)4187-DC (10 June 2022)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Downloaded from Arrow.com.

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Not Recommended For New Design
Category	Inductive Sensors
Series	120253
Description	Contrinex Inductive Sensor, C23 (20 x 32mm) Fully Stainless Steel, 7mm Operating Distance, Embeddable, PNP, NO, 0.2m 3-wire PVC Cable, 3-pin M8 Connector
IP Rating	IP68, IP69K
Product Name	Contrinex
Type	Inductive
UPC	191130064885

Electrical

Output	NO
Polarity	PNP
Switching Frequency	≤ 180 Hz

Physical

Connection	Cable (PVC 0.2m, 3-wire), Connector (M8, 3-pin)
Housing Size	20 x 32mm
Material - Housing	Stainless Steel
Material - Sensing Face	Stainless Steel

Downloaded from Arrow.com.

Mounting Style	Embeddable
Net Weight	854.000/g
Operating Distance	7mm
Output	NO
Sensor Housing Size	C23
Temperature Range - Operating	-25° to +85°C

Downloaded from Arrow.com.