





REV.	ECR/ECN No.	DESCRIPTION	DRAWN/DATE	CHECKED/DATE	APPROVED/DATE
F		UPDATE FRAME	Staven 2020-11-13	Staven 2020-11-13	Biao 2020-11-13
G	ECN2022112	UPDATE CPK SYMBOLS	Abner 2022-07-20	Staven 2022-07-20	Sam 2022-07-20




NOTES:

- 1、MATERIAL: SUS 304-H T=0.15mm;
- 2、ALLOW BURR 0.03mm Max.;
- 3、PLATING: Au 2u" SURFACE PLATING OVER CONTACT AREAS,
Au 2u" SURFACE PLATING OVER SOLDER AREAS,
Ni 40-120u" UNDER PLATING OVER ALL.
- 4、"▼"THE SYMBOL IS REPRESENTED AS CPK AND $\bar{X}$ -R.

TABLE:

PART NUMBER	A	B	C	D
Z00D-4G7L1-11000	$4.8^{+0.3}_{-0.05}$	$1.5^{+0.0}_{-0.3}$	1.50	$3.90^{+0}_{-0.20}$
Z007-4G7L1-11000	$5.2^{+0.3}_{-0.05}$	$1.9^{+0.0}_{-0.3}$	1.05	$3.90^{+0}_{-0.20}$
Z00C-4G7L1-11000	$7.5^{+0.3}_{-0.05}$	$4.2^{+0.0}_{-0.3}$	1.50	$3.90^{+0}_{-0.20}$
Z00F-4G7L1-11000	$9.0^{+0.3}_{-0.05}$	$5.7^{+0.0}_{-0.3}$	0.80	$3.90^{+0}_{-0.5}$
Z00N-4G7L1-11000	$6.3^{+0.3}_{-0.05}$	$3.0^{+0.15}_{-0.15}$	1.50	$3.90^{+0}_{-0.15}$
Z00E-4G7L1-11000	$4.0^{+0.3}_{-0.05}$	$0.7^{+0.15}_{-0.15}$	1.50	$3.90^{+0}_{-0.15}$
Z00X-4G7L1-11000-E000	$5.6^{+0.3}_{-0.05}$	$2.3^{+0.15}_{-0.15}$	1.50	$3.90^{+0}_{-0.15}$

UNLESS OTHERWISE SPECIFIED TOLERANCES				ANGLE OF PROJECTION 		 Amphenol Aorora Technology (Huizhou) Co.,Ltd				
X.	±0.30	X. *	± 5'			TITLE: SPRING				
X.X	±0.25	X.X *	± 4'							
X.XX	±0.20	X.XX *	± 3'							
X.XXX	±0.15	X.XXX *	± 2'	DOC TYP Customer Drw		SIZE PART NUMBER: SEE TABLE REV. G				
LINEAR DIMS		ANGLES DIMS		DRAWN DATE Abner 2022-07-20						
DWG NO.: A-S0198				DESIGN DATE Abner 2022-07-20						
MATERIAL		SEE NOTES		CHECKED DATE Stoven 2022-07-20						
FINISHED		SEE NOTES		APPROVED DATE Sam 2022-07-20		SCALE		1:1	UNIT : mm	SHEET 1 OF 1

