

Technical data sheet

Article number:
323-00104

MA40-22/6



Product Group	Heat shrinkable tubing 4:1 - Flame retardant
Product Family	MA40 - medium wall adhesive lined
Material	Polyolefin, cross-linked (PO-X)
Colour	Black (BK)
Adhesive	Hot melt adhesive
Dielectric Strength [Test method]	15 kV/mm [IEC 60243-1]
Elongation at break (min.) [Test method]	350 % [ASTM D2671]
Elongation At Heat Aging	300 %
Heat Aging Test [Test method]	168h/150°C [ASTM D2671]
Longitudinal Change After Shrinkage	-10% max.
Min. Shrink Temperature - °C	+120 °C
Minimum Tensile Strength At Heat Aging	12 MPa
Operating Temperature	-55 °C to +110 °C
Package Content	5 pcs.
Package Content packed in	lengths
Recov. Ø d max.	6.0 mm
Shrink Ratio	up to 4:1
Specifications	DIN EN ISO 8580, DNV
Supplied Ø D min.	22.0 mm
Tensile Strength [Test method]	12 MPa [ASTM D2671]
Wall (WT)	2.4 mm

