

CK2,5-M-4 AG - Crimp contact

1409208

<https://www.phoenixcontact.com/us/products/1409208>



Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.



Crimp contact, Range of articles: PRC 35, Crimp contact, max. conductor cross section: 4 mm², rated voltage: 690 V AC, rated current: 32 A, Connection method: Crimp connection, Contact connection type: Pin. Crimp the wire with the crimp contact in accordance with DIN EN 60352-2

Product Description

Pin contact for PRC device connectors

Your advantages

- Crimp contacts for PRC device connectors for assembly
- 3 variants for wire cross sections of 2.5 / 4.0 / 6.0 mm²

Commercial Data

Item number	1409208
Packing unit	1 pc
Minimum order quantity	100 pc
Sales Key	AB03
Product Key	ABLCEA
Catalog Page	Page 77 (NTK-2014)
GTIN	4046356864473
Weight per Piece (including packing)	2.102 g
Weight per Piece (excluding packing)	2.105 g
Customs tariff number	85389099
Country of origin	DE

CK2,5-M-4 AG - Crimp contact

1409208

<https://www.phoenixcontact.com/us/products/1409208>



Technical Data

Notes

General	Crimp the wire with the crimp contact in accordance with DIN EN 60352-2
General	Please remove the crimping pliers locator

Safety note

Safety note	<ul style="list-style-type: none">• WARNING: Commission properly functioning products only. The products must be regularly inspected for damage. Decommission defective products immediately. Replace damaged products. Repairs are not possible.• WARNING: Only electrically qualified personnel may install and operate the product. They must observe the following safety notes. The qualified personnel must be familiar with the basics of electrical engineering. They must be able to recognize and prevent danger. The relevant symbol on the packaging indicates that only personnel familiar with electrical engineering are allowed to install and operate the product.• WARNING: The connectors may not be plugged in or disconnected under load. Ignoring the warning or improper use may damage persons and/or property.• Assembled products may not be manipulated or improperly opened.• Only use mating connectors that are specified in the technical data of the standards listed (e.g. the ones listed in the product accessories online at phoenixcontact.com/products).• When using the product in direct connection with third-party manufacturers, the user is responsible.• For operating voltages > 50 V AC, conductive connector housings must be grounded• Ensure that the protective or functional ground has been properly connected.• VDE 0100/1.97 § 411.1.3.2 and DIN EN 60 204/11.98 § 14.1.3 are applicable when combining several circuits in a cable and/or connector• Observe the corresponding technical data. You will find information:<ul style="list-style-type: none">o On the producto On the packing labelo In the supplied documentationo Online at phoenixcontact.com/products under the product• Only use tools recommended by Phoenix Contact• The installation notes/Design In documents online on the download page at phoenixcontact.com/products must be observed for this product.• Use a protective cap to protect connectors that are not in use. The suitable accessories are available online in the accessory section of the product at phoenixcontact.com/products• Operate the connector only when it is fully plugged in.• Operate the connector only when it is fully plugged in and interlocked.
-------------	---

CK2,5-M-4 AG - Crimp contact



1409208

<https://www.phoenixcontact.com/us/products/1409208>

- Ensure that when laying the cable, the tensile load on the connectors does not exceed the upper limit specified in the standards.
- Observe the minimum bending radius of the cable. Lay the cable without twisting it.
- The connector warms up in normal operation. Depending on the ambient conditions, the surface of the connector can continue to warm up. In this case, the user is responsible for posting warnings (e.g. DIN EN ISO 13732-1:2008-12).

Mounting

Connection method	Crimp connection
-------------------	------------------

Product properties

Product type	Crimp contact
Product family	PRC 35

Insulation characteristics

Protection class	II
Degree of pollution	2

Connection data

Connection method	Crimp connection
Contact connection type	Pin

Material specifications

Flammability rating according to UL 94	V0
Contact material	Cu alloy
Contact surface material	Ag

Dimensions

Width	5.6 mm
Height	5.6 mm
Length	31.2 mm

Electrical properties

Nominal voltage ATD	690 V AC in accordance with IEC 61984
	600 V AC In accordance with UL 2238
Rated current	32 A (in accordance with IEC 61984)
	25 A (in accordance with IEC 61535)

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	100
-----------------------------	-----

Environmental and real-life conditions

CK2,5-M-4 AG - Crimp contact

1409208

<https://www.phoenixcontact.com/us/products/1409208>



Ambient conditions

Ambient temperature (assembly)	5 °C ... 85 °C
--------------------------------	----------------

CK2,5-M-4 AG - Crimp contact

1409208

<https://www.phoenixcontact.com/us/products/1409208>



Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1409208>



EAC

Approval ID: B.01687

CK2,5-M-4 AG - Crimp contact

1409208

<https://www.phoenixcontact.com/us/products/1409208>



Classifications

ECLASS

ECLASS-11.0	27440109
ECLASS-12.0	27440109
ECLASS-13.0	27440109

ETIM

ETIM 8.0	EC003569
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

CK2,5-M-4 AG - Crimp contact

1409208

<https://www.phoenixcontact.com/us/products/1409208>



Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

CK2,5-M-4 AG - Crimp contact

1409208

<https://www.phoenixcontact.com/us/products/1409208>



Accessories

CRIMPFOX-TC 4 - Crimping pliers

1212113

<https://www.phoenixcontact.com/us/products/1212113>



Crimping pliers, for CK 1,6-ED..., CK 2,5-ED..., CK 4,0-ED... turned contacts, 4 marked die stations, unlockable pressure lock, lateral entry, incl. positioning tool

Phoenix Contact 2023 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com