

6

5

4

3





2

1

Rev	AWO #	Description	Date	Appr
-	7790	RELEASED	5/10/07	

APPROVED: \_\_\_\_\_

DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_



PCB LAYOUT

**SPECIFICATIONS:****Material:**

Insulator: Hi-temp thermoplastic, rated UL 94V-0

Insulator color: Ivory

Contacts: Brass

**Plating:**

Tin over Nickel underplate overall

**Electrical:**

Operating voltage: 100 VAC max

Current rating: 1.5 Amps max

Contact resistance: 20 mohms max

Insulation resistance: 500 Mohms min

Dielectric withstanding voltage: 500 VAC for 1 minute

**Temperature Rating:**

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant.



A=.060 [1.50] X No. of Positions -1  
 B=.060 [1.50] X No. of Positions + .051 [1.30]

**ADAM TECH**

909 Railway Avenue, Union, NJ 07083  
 Phone: 908-687-5000 Fax: 908-687-5710

MX1.5mm WAFER 180°

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES				Holes			
.X	± .10	ØX	± .10	.X	± .10	ØX	± .10
.XX	± .020	ØXX	± .015	.XX	± .020	ØXX	± .015
.XXX	± .015	ØXXX	± .010	.XXX	± .015	ØXXX	± .010
APPROVALS				DATE			
DRAWN	BW			5/10/07			
CHECKED							
APPROVED							
TITLE				SIZE			
PART NO.				REV.			
15SH-B-XX-TS-SMT				-			
SCALE: NTS				SHEET 1 OF 1			