

# Specifications

## Eaton KR-5R5V104-R

Eaton KR supercapacitor, 5.5 V, Vertical,  
Capactiance 0.1

### General specifications

<b>PRODUCT NAME</b>	Eaton KR coin cell supercapacitors
<b>CATALOG NUMBER</b>	KR-5R5V104-R
<b>UPC</b>	051712536370
<b>PRODUCT HEIGHT</b>	4.3 mm
<b>PRODUCT DIAMETER</b>	11.5 mm
<b>PRODUCT WEIGHT</b>	1.4 g
<b>COMPLIANCES</b>	RoHS Compliant

## Product specifications

PACKING	Bulk
CONTACT CONFIGURATION	Vertical
TERMINALS	Through hole
SHAPE	Round
DC EQUIVALENT SERIES RESISTANCE (ESR)	75 $\Omega$
OPERATING TEMPERATURE RANGE	-25 °C to +70 °C
SERIES	KR
MAX VOLTAGE	5.5 V
CAPACITANCE	0.1 F
ENERGY	1.5 J
CAPACITANCE END OF LIFE RATING	70%
ESR END OF LIFE RATING	400%
GRADE	Commercial

## Resources

APPLICATION NOTES	<a href="#">Supercapacitor soldering guidelines</a>
BROCHURES	<a href="#">Supercapacitor coin cell cross reference guide</a> <a href="#">Coin cell supercapacitor product aid</a>
MANUALS AND USER GUIDES	<a href="#">Methods for measuring capacitance, inflow current, internal resistance and ESR</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - KR-5R5V104-R</a> <a href="#">Eaton KR supercapacitor data sheet</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

