




HONEYWELL PART NUMBER
1SX36-T
PRODUCT CODE VDA3650

REV	DOCUMENT	CHANGED BY	CHECK
10	0038446	KVB 20MAY08	BLR



- NOTE -
- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .188±.002 CENTERS
 - 2 - TERMINALS ARE PLATED FOR SOLDERING
 - 3 - SWITCH WILL WITHSTAND TEMPERATURE OF 250° F
 - 4 - SWITCH HAS A GREATER OVERTRAVEL THAN STANDARD CONSTRUCTION. ADDITIONAL OVERTRAVEL WILL TEND TO REDUCE MECHANICAL LIFE.

RELEASE NO.	PR-5629
REPLACES	-

CHARACTERISTICS		ELECTRICAL DATA			DESIGN UNITS: INCH			DRAWN	SPK	30NOV07		Honeywell						
OPERATING FORCE — — — — 5 OZ MAX		CONTACT ARRANGEMENT SPDT			TOLERANCES UNLESS NOTED:			CHECK	RJ	30NOV07								
RELEASE FORCE— — — — — 1 OZ MIN		28 VOLTS DC RATING			NO PLACE X ±			THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.				TITLE						
DIFFERENTIAL TRAVEL— — — .005 MAX					ONE PLACE .X ±													
OVERTRAVEL — — — — — .010 MIN		SEA LEVEL 50,000 FT			TWO PLACE .XX ±													
		INDUCTIVE 4 AMP 2.5 AMP			THREE PLACE .XXX ±													
		RESISTIVE 7 AMP 7 AMP			FOUR PLACE .XXXX ±			INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY				SIZE	TYPE	DRAWING NAME		REV		
		MAXIMUM INRUSH 24 AMP			ANGLES ±							B	I	1SX36-T		10		
		APPROVALS	KEMA, CE	7A 250V~ T125 5E4		05	THIRD ANGLE PROJECTION	RASTER						SCALE	-	WEIGHT:.003 LB MAX	SHEET 1 OF 1	
			UL, CSA	7A 250 VAC		L7												