

Search:

Go

Connectors

Sockets /
EdgecardsCable
Assemblies

Antennas

Fiber Optic
ProductsPrinted Circuit
ProductsAutomation /
IndustrialLighting
ProductsHome: [Datasheet](#)

Part Number: 71660-9680



Series image - Reference only

Status:

Contact Molex

Series:

[71660](#)

Category:

Molex Parts

Go to [Part Detail](#)

CHECK DISTRIBUTOR INVENTORY

[Add to My Parts](#)

Specifications & Other Documents:

Documents not available online

Note - Please disable browser pop-up blockers to view documents on www.molex.comQuestions on Product Environmental Compliance? Email productcompliance@molex.com[EU RoHS](#) : ELV and RoHS Compliant[China RoHS](#) : ☐[REACH SVHC](#) : Contains SVHC: No[Low-Halogen Status](#) : Low-Halogen

Product Compliance Statement

Application Tooling ♦♦

[FAQ](#)

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)

Part Detail

SHOW ALL

General

Status	Contact Molex
Category	Molex Parts
Series	71660
UPC	800753785366

Physical

Flammability	94V-0
Net Weight	4.395/g

Agency Certification

Please find UL Certificates by searching the UL Database using the Molex Series Number. [Click here to visit the UL Database](#)

CSA	LR19980
UL	E29179

Solder Process Data

Duration at Max. Process Temperature (seconds)	40
Lead-free Process Capability	SMC & Wave Capable (TH only)
Max. Cycles at Max. Process Temperature	3
Process Temperature max. C	260

Material Info

- Wire-to-Board
- Board-to-Board
- Wire-to-Wire
- Input/Output (IO)
- FFC/FPC
- Sockets

- Fiber Optic Products
- Antennas
- Industrial Automation
- Membrane Switches
- Copper Flex
- PCB Assemblies
- Woodhead Electrical
- Solid State Lighting

- Contact Us
- Catalog
- Cross-Reference
- Industries
- Literature
- Product Name

- About Us
- Careers
- ecocare
- Investors
- Press Room
- Shows & Events
- Supplier Portal

- Feedback
- Help
- Legal Disclaimer
- View Mobile Site
- Privacy Policy
- Sitemap

Stay Connected with Molex:

□ □ □
□ □ □

Copyright 2014