


HONEYWELL
PART NUMBER

311SX4-H391

PRODUCT CODE

VDS0039

REV	DOCUMENT	CHANGED BY	CHECK
4	0038558	SS 08MAY08	BLR



NOTES

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF Ø.087 MAX ON $.188 \pm .002$ CENTERS
- 2 - TERMINALS ARE PLATED FOR SOLDERING
- 3 - SWITCH WILL WITHSTAND TEMPERATURE OF 250°F
- 4 CHARACTERISTICS ARE TAKEN AT POINT "A"

RELEASE NO.	PR-21210
REPLACES	X96072-SX

CHARACTERISTICS (4)

OPERATING FORCE -- 60 GRAMS MAX

RELEASE FORCE -- 11 GRAMS MIN

DIFFERENTIAL TRAVEL -- .015 MAX

OVERTRAVEL -- .010 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
SPDT

	28 VOLTS DC RATING	115 VOLTS AC, 60 CPS
SEA LEVEL	50,000 FT	SEA LEVEL
INDUCTIVE	3 AMP	2 AMP
RESISTIVE	5 AMP	4 AMP

APPROVALS	KEMA, CE	5A 250 V ~ T125	5E4	CE
	UL, CSA	5A 250 VAC	UL	BRAND L4L

DESIGN UNITS: INCH

TOLERANCES UNLESS NOTED:

NO PLACE	X	±
ONE PLACE	.X	±
TWO PLACE	.XX	±
THREE PLACE	.XXX	±
FOUR PLACE	.XXXX	±
ANGLES		±

THIRD ANGLE PROJECTION



DRAWN

SPK

26FEB08

CHECK

RJ

26FEB08

THIS DRAWING COVERS A PROPRIETARY ITEM
AND IS THE PROPERTY OF HONEYWELL.
THIS DRAWING IS NOT TO BE COPIED OR USED
WITHOUT THE PERMISSION OF HONEYWELL.

INTERPRET PER ANSI Y14.5M-1982
OTHER HONEYWELL ENGINEERING
STANDARDS MAY APPLY

RASTER

Honeywell

TITLE

SWITCH - BASIC

SIZE

TYPE

DRAWING NAME

REV

B**I****311SX4-H391****4**

SCALE

-

WEIGHT: .003 LB MAX

SHEET 1 OF 1