



# Mechanical Rotating Crimper, #8 AWG - #4/0 AWG Copper

By Burndy  
Catalog # [MRC840](#)

Crimper, #8-4/0 AWG CU.



### Features

- Spring loaded mechanism locks die wheel into position
- Press mechanism to release
- Rotating die wheel color coded marked with AWG sizes
- Steel jaws

### Application

- Crimping

### General

Application - For Use On	Copper Terminals and Splices
Catalog Number	MRC840
Die Type	Rotating Die Wheel
EU RoHS Indicator	Yes
Sub Brand	HYTOOL
Tool Type	Mechanical Rotating Crimper
Trade Name	HYTOOL™
UPC	781810192504
UPC 12 Digit	7818101925044

### Dimensions

Dimensions	26.00 in x 8.00 in x 1.50 in
Height	1.5 in
Length	26 in
Weight	8.25 lb
Width	8 in

### Conductor Related

Crimping Ranges	Copper: #8 AWG- #4/0 AWG
-----------------	--------------------------

### Certifications And Compliance

Standards - RoHS Compliance	EX
Status	

### Logistics

Minimum Pack Quantity	1
Package Contents	Tool only

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Catalogs - Section N - Tooling](#)  
[Installation Manuals - BUR\\_50097800\\_MRC840](#)  
[Product Cross Section Image\(s\) - BUR\\_MRC840\\_lineart](#)  
[Sales Drawings - SE..211280-01](#)



A proud member of the Hubbell Family.