OMRON Industrial Automation



E32-T14 2M

Fiber optic sensor head, through-beam, long distance detection, square, side-view, R25 fiber, 2 m cable

Downloaded from Arrow.com.

Specifications

Sensing method	Through-beam
Shape	Square
Product Width (unpacked)	10.5 mm
Product Depth (unpacked)	8 mm
Product Height (unpacked)	25.2 mm
Application	Long distance detection
Features	Built?in lens
Temperature range	-40-70 °C
Sensing distance	4000 mm
Cable length	2 m
Sleeve diameter	-8888 mm
Sleeve length	-8888 mm
Bending radius	25 mm
Free cut	✔
Material core	Plastic
Degree of protection (IP)	IP67
Sensing surface orientation	Side-view
Material sheath	Polyethylene

Downloaded from Arrow.com.

Related products



E3X-ZV and E3X-MZV
Smart Fiber Amplifier



E3NX-CA
High-performance color mark sensor



E3NX-CA
High-performance color mark sensor



E3NX-MA
Smart Fiber Amplifier Units



E3X-NA
Digital fiber amplifier with potentiometer adjustment



E3NX-FA
High-performance digital fiber amplifier

Downloads

CAD Library



E32-LT/LD Hex-shaped Fiber Unit
Brochure
EN PDF 6.35 MB



Fiber Sensor Selection
Selection Guide
EN PDF 15.9 MB

Downloaded from Arrow.com.

TERMS OF WEBSITE USE

This PDF document was created from the European OMRON Industrial Automation website on 6 August, 2026. Click here for terms of use.

OMRON

INDUSTRIAL AUTOMATION | INDUSTRIAL.OMRON.EU

Downloaded from Arrow.com.