

1N5221B THRU 1N5278B

SILICON ZENER DIODES
500mW, 2.4 THRU 170 VOLT
5% TOLERANCE



DO-35 CASE



www.centra-semi.com

DESCRIPTION:

The CENTRAL SEMICONDUCTOR 1N5221B series silicon Zener diodes are highly reliable voltage regulators designed for use in industrial, commercial, entertainment and computer applications.

MARKING: Devices shall either be marked with the prefix 'C' followed by the full part number or by the marking code in the Electrical Characteristics Table.

MAXIMUM RATINGS: (T_L=75°C)

Power Dissipation

Operating and Storage Junction Temperature

V_Z Tolerance: Part number with "B" suffix

V_Z Tolerance: Part number with "C" suffix

V_Z Tolerance: Part number with "D" suffix

SYMBOL

P_D

T_J, T_{stg}

500

-65 to +200

±5

±2

±1

UNITS

mW

°C

%

%

%

ELECTRICAL CHARACTERISTICS: (T_A=25°C) V_F=1.2V MAX @ I_F=200mA (for all types)

TYPE	ZENER VOLTAGE V _Z @ I _{ZT}			TEST CURRENT I _{ZT} mA	MAXIMUM ZENER IMPEDANCE			MAXIMUM REVERSE CURRENT		MAXIMUM TEMPERATURE COEFFICIENT ∂V _Z %/°C	MARKING CODE
	MIN	NOM	MAX		Z _{ZT} @ I _{ZT}	Z _{ZK} @ I _{ZK}	I _R @ V _R				
	V	V	V		Ω	Ω	mA	μA	V		
1N5221B	2.280	2.4	2.520	20	30	1200	0.25	100	1.0	-0.085	C5221B
1N5222B	2.375	2.5	2.625	20	30	1250	0.25	100	1.0	-0.085	C5222B
1N5223B	2.565	2.7	2.835	20	30	1300	0.25	75	1.0	-0.080	C5223B
1N5224B	2.660	2.8	2.940	20	30	1400	0.25	75	1.0	-0.080	C5224B
1N5225B	2.850	3.0	3.150	20	29	1600	0.25	50	1.0	-0.075	C5225B
1N5226B	3.135	3.3	3.465	20	28	1600	0.25	25	1.0	-0.070	C5226B
1N5227B	3.420	3.6	3.780	20	24	1700	0.25	15	1.0	-0.065	C5227B
1N5228B	3.705	3.9	4.095	20	23	1900	0.25	10	1.0	-0.060	C5228B
1N5229B	4.085	4.3	4.515	20	22	2000	0.25	5.0	1.0	±0.055	C5229B
1N5230B	4.465	4.7	4.935	20	19	1900	0.25	5.0	2.0	±0.030	C5230B
1N5231B	4.845	5.1	5.355	20	17	1600	0.25	5.0	2.0	±0.030	C5231B
1N5232B	5.320	5.6	5.880	20	11	1600	0.25	5.0	3.0	+0.038	C5232B
1N5233B	5.700	6.0	6.300	20	7.0	1600	0.25	5.0	3.5	+0.038	C5233B
1N5234B	5.890	6.2	6.510	20	7.0	1000	0.25	5.0	4.0	+0.045	C5234B
1N5235B	6.460	6.8	7.140	20	5.0	750	0.25	3.0	5.0	+0.050	C5235B
1N5236B	7.125	7.5	7.875	20	6.0	500	0.25	3.0	6.0	+0.058	C5236B
1N5237B	7.790	8.2	8.610	20	8.0	500	0.25	3.0	6.5	+0.062	C5237B
1N5238B	8.265	8.7	9.135	20	8.0	600	0.25	3.0	6.5	+0.065	C5238B
1N5239B	8.645	9.1	9.555	20	10	600	0.25	3.0	7.0	+0.068	C5239B
1N5240B	9.500	10	10.50	20	17	600	0.25	3.0	8.0	+0.075	C5240B
1N5241B	10.45	11	11.55	20	22	600	0.25	2.0	8.4	+0.076	C5241B
1N5242B	11.40	12	12.60	20	30	600	0.25	1.0	9.1	+0.077	C5242B
1N5243B	12.35	13	13.65	9.5	13	600	0.25	0.5	9.9	+0.079	C5243B
1N5244B	13.30	14	14.70	9.0	15	600	0.25	0.1	10	+0.082	C5244B
1N5245B	14.25	15	15.75	8.5	16	600	0.25	0.1	11	+0.082	C5245B
1N5246B	15.20	16	16.80	7.8	17	600	0.25	0.1	12	+0.083	C5246B

R5 (8-May 2020)

1N5221B THRU 1N5278B

SILICON ZENER DIODES
500mW, 2.4 THRU 170 VOLT
5% TOLERANCE




ELECTRICAL CHARACTERISTICS - Continued: ($T_A=25^\circ\text{C}$) $V_F=1.2\text{V MAX @ } I_F=200\text{mA}$ (for all types)

TYPE	ZENER VOLTAGE V _Z @ I _{ZT}			TEST CURRENT	MAXIMUM ZENER IMPEDANCE			MAXIMUM REVERSE CURRENT		MAXIMUM TEMPERATURE COEFFICIENT	MARKING CODE
	MIN	NOM	MAX		I _{ZT}	Z _{ZT} @ I _{ZT}	Z _{ZK} @ I _{ZK}	I _R @ V _R	ΘV _Z		
	V	V	V		mA	Ω	Ω	mA	μA	V	
1N5247B	16.15	17	17.85	7.4	19	600	0.25	0.1	13	+0.084	C5247B
1N5248B	17.10	18	18.90	7.0	21	600	0.25	0.1	14	+0.085	C5248B
1N5249B	18.05	19	19.95	6.6	23	600	0.25	0.1	14	+0.086	C5249B
1N5250B	19.00	20	21.00	6.2	25	600	0.25	0.1	15	+0.086	C5250B
1N5251B	20.90	22	23.10	5.6	29	600	0.25	0.1	17	+0.087	C5251B
1N5252B	22.80	24	25.20	5.2	33	600	0.25	0.1	18	+0.088	C5252B
1N5253B	23.75	25	26.25	5.0	35	600	0.25	0.1	19	+0.089	C5253B
1N5254B	25.65	27	28.35	4.6	41	600	0.25	0.1	21	+0.090	C5254B
1N5255B	26.60	28	29.40	4.5	44	600	0.25	0.1	21	+0.091	C5255B
1N5256B	28.50	30	31.50	4.2	49	600	0.25	0.1	23	+0.091	C5256B
1N5257B	31.35	33	34.65	3.8	58	700	0.25	0.1	25	+0.092	C5257B
1N5258B	34.20	36	37.80	3.4	70	700	0.25	0.1	27	+0.093	C5258B
1N5259B	37.05	39	40.95	3.2	80	800	0.25	0.1	30	+0.094	C5259B
1N5260B	40.85	43	45.15	3.0	93	900	0.25	0.1	33	+0.095	C5260B
1N5261B	44.65	47	49.35	2.7	105	1000	0.25	0.1	36	+0.095	C5261B
1N5262B	48.45	51	53.55	2.5	125	1100	0.25	0.1	39	+0.096	C5262B
1N5263B	53.20	56	58.80	2.2	150	1300	0.25	0.1	43	+0.096	C5263B
1N5264B	57.00	60	63.00	2.1	170	1400	0.25	0.1	46	+0.097	C5264B
1N5265B	58.90	62	65.10	2.0	185	1400	0.25	0.1	47	+0.097	C5265B
1N5266B	64.60	68	71.40	1.8	230	1600	0.25	0.1	52	+0.097	C5266B
1N5267B	71.25	75	78.75	1.7	270	1700	0.25	0.1	56	+0.098	C5267B
1N5268B	77.90	82	86.10	1.5	330	2000	0.25	0.1	62	+0.098	C5268B
1N5269B	82.65	87	91.35	1.4	370	2200	0.25	0.1	68	+0.099	C5269B
1N5270B	86.45	91	95.55	1.4	400	2300	0.25	0.1	69	+0.099	C5270B
1N5271B	95.00	100	105.0	1.3	500	2600	0.25	0.1	76	+0.110	C5271B
1N5272B	104.5	110	115.5	1.1	750	3000	0.25	0.1	84	+0.110	C5272B
1N5273B	114.0	120	126.0	1.0	900	4000	0.25	0.1	91	+0.110	C5273B
1N5274B	123.5	130	136.5	0.95	1100	4500	0.25	0.1	99	+0.110	C5274B
1N5275B	133.0	140	147.0	0.90	1300	4500	0.25	0.1	106	+0.110	C5275B
1N5276B	142.5	150	157.5	0.85	1500	5000	0.25	0.1	114	+0.110	C5276B
1N5277B	152.0	160	168.0	0.80	1700	5500	0.25	0.1	122	+0.110	C5277B
1N5278B	161.5	170	178.5	0.74	1900	5500	0.25	0.1	129	+0.110	C5278B

DO-35 CASE - MECHANICAL OUTLINE

SYMBOL	DIMENSIONS			
	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	0.018	0.022	0.46	0.56
B	0.120	0.200	3.05	5.08
C	0.060	0.090	1.52	2.29
D	1.000	-	25.40	-

DO-35 (REV: R1)



R5 (8-May 2020)

www.centrasemi.com

OUTSTANDING SUPPORT AND SUPERIOR SERVICES



PRODUCT SUPPORT

Central's operations team provides the highest level of support to insure product is delivered on-time.

- Supply management (Customer portals)
- Inventory bonding
- Consolidated shipping options
- Custom bar coding for shipments
- Custom product packing

DESIGNER SUPPORT/SERVICES

Central's applications engineering team is ready to discuss your design challenges. Just ask.

- Free quick ship samples (2nd day air)
- Online technical data and parametric search
- SPICE models
- Custom electrical curves
- Environmental regulation compliance
- Customer specific screening
- Up-screening capabilities
- Special wafer diffusions
- PbSn plating options
- Package details
- Application notes
- Application and design sample kits
- Custom product and package development

REQUESTING PRODUCT PLATING

1. If requesting Tin/Lead plated devices, add the suffix "TIN/LEAD" to the part number when ordering (example: 2N2222A TIN/LEAD).
2. If requesting Lead (Pb) Free plated devices, add the suffix "PBFREE" to the part number when ordering (example: 2N2222A PBFREE).

CONTACT US

Corporate Headquarters & Customer Support Team

Central Semiconductor Corp.
145 Adams Avenue
Hauppauge, NY 11788 USA
Main Tel: (631) 435-1110
Main Fax: (631) 435-1824
Support Team Fax: (631) 435-3388
www.centrasemi.com

Worldwide Field Representatives:
www.centrasemi.com/wwreps

Worldwide Distributors:
www.centrasemi.com/wwdistributors

For the latest version of Central Semiconductor's **LIMITATIONS AND DAMAGES DISCLAIMER**, which is part of Central's Standard Terms and Conditions of sale, visit: www.centrasemi.com/terms

Product End of Life Notification

PDN ID:	PDN01089
Notification Date:	5/02/18
Last Buy Date:	11/02/18
Last Shipment Date	5/02/19

Summary: All high voltage 500mW Zener diodes in the DO-35 package are discontinued and now classified as End of Life (EOL).

Although Central Semiconductor Corp. makes every effort to continue to produce devices that have been proclaimed EOL (End of Life) by other manufacturers, it is an accepted industry practice to discontinue certain devices when customer demand falls below a minimum level of sustainability. Accordingly, the following product(s) have been transitioned to End of Life status as part of Central's ongoing Product Management Process. Any replacement products are noted below. The effective date for placing last purchase orders will be six (6) months from the date of this notice and twelve (12) months from the notice date for final shipments, and minimum order quantities may apply. The last purchase and shipment dates may be extended if inventory is available.

<u>Central Part Number</u>	<u>Replacement</u>
1N5263B BK	N/A
1N5263B TR	N/A
1N5264B BK	N/A
1N5264B TR	N/A
1N5265B BK	N/A
1N5265B TR	N/A
1N5266B BK	N/A
1N5266B TR	N/A
1N5267B BK	N/A
1N5267B TR	N/A
1N5268B AP	N/A
1N5268B BK	N/A
1N5268B TR	N/A
1N5269B AP	N/A
1N5269B BK	N/A
1N5269B TR	N/A
1N5270B AP	N/A
1N5270B BK	N/A
1N5270B TR	N/A
1N5271B AP	N/A
1N5271B BK	N/A
1N5271B TR	N/A
1N5272B AP	N/A
1N5272B BK	N/A
1N5272B TR	N/A
1N5273B AP	N/A
1N5273B BK	N/A
1N5273B TR	N/A
1N5274 TR	N/A
1N5274B BK	N/A
1N5274B TR	N/A
1N5275B BK	N/A
1N5275B TR	N/A
1N5276B BK	N/A
1N5276B TR	N/A
1N5277B BK	N/A
1N5277B TR	N/A
1N5278B BK	N/A

*** CONTINUED ***

DISCLAIMER: This End of Life (EOL) notification is in accordance with JEDEC standard JESD48 - Product Discontinuance. Central Semiconductor Corp. will make every effort to offer life-time buy (LTB) opportunities and/or offer replacement devices to existing customers for discontinued devices, however, one or both may not be possible for all devices. Please contact your local Central Semiconductor sales representative for LTB opportunities/additional information.



<http://www.centrasemi.com>

Product End of Life Notification

PDN ID:	PDN01089
Notification Date:	5/02/18
Last Buy Date:	11/02/18
Last Shipment Date	5/02/19

*** CONTINUED FROM PRIOR PAGE ***

<u>Central Part Number</u>	<u>Replacement</u>
1N5278B TR	N/A
1N5279B BK	N/A
1N5279B TR	N/A
1N5280B BK	N/A
1N5280B TR	N/A
1N5281B BK	N/A
1N5281B TR	N/A

Central would be happy to assist you by providing additional information or technical data to help locate an alternate source if we have no replacement available. Please email your requests to engineering@centrasemi.com.

DISCLAIMER: This End of Life (EOL) notification is in accordance with JEDEC standard JESD48 - Product Discontinuance. Central Semiconductor Corp. will make every effort to offer life-time buy (LTB) opportunities and/or offer replacement devices to existing customers for discontinued devices, however, one or both may not be possible for all devices. Please contact your local Central Semiconductor sales representative for LTB opportunities/additional information.