







78 POSITIONS




OPTION A




OPTION C



OPTION E



OPTION H



REVISIONS

REV.	DESCRIPTION	DATE	BY
1	ORIGINAL	DRAWN DATE	

SERIES _____ MHHDD - VERTICAL P.C.TAIL

POSITIONS _____

15 - 15 POSITIONS
26 - 26 POSITIONS
44 - 44 POSITIONS
62 - 62 POSITIONS
78 - 78 POSITIONS

GENDER _____

M - MALE

SHELL PLATING _____

N - NICKEL PLATING

CONTACT TYPE _____

S - STAMPED

HARDWARE OPTIONS _____

A - 3.05MM THROUGH HOLE
C - #4-40 BOARDSIDE CLINCH NUT, L=2.5MM, NI PLATING
E - #4-40 BOARDSIDE CLINCH NUT, NI PLATING, BOARDLOCK, TIN PLATING
H - #4-40 THREADED STANDOFF, NI PLATING, BOARDLOCK, TIN PLATING

CONTACT PLATING _____

I - GOLD FLASH

SPECIFICATIONS

CURRENT RATING: 3A
WITHSTANDING VOLTAGE: 500VAC FOR 1 MIN
INSULATION RESISTANCE: 1000 M Ω MIN.
CONTACT RESISTANCE: 30 m Ω MAX.
TEMPERATURE RANGE: -55°C TO 105°C

INSULATOR MATERIAL: PBT+30% G.F.
INSULATOR COLOR: BLACK
SHELL MATERIAL: STEEL
CONTACT MATERIAL: BRASS
CONTACT PLATING: GOLD FLASH
HARDWARE MATERIAL: BRASS

POSITIONS	A	B	C	D	E	F	G	H
15	30.81	24.99	16.92	19.28	12.55	8.20	2.29	1.98
26	39.14	33.32	25.25	27.51	12.55	8.20	2.29	1.98
44	53.04	47.04	38.96	41.28	12.55	8.20	2.29	1.98
62	69.32	63.50	55.42	57.40	12.55	8.20	2.41	1.98
78	67.20	61.10	52.70	55.10	15.30	11.30	2.41	2.08

MH
CONNECTORS

MH CONNECTORS
LTD.

RoHS
COMPLIANT

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF EDAC, AND SHALL NOT BE REPRODUCED, OR COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN BY	V.K.	MHHDD SERIES, D-SUB, HIGH DENSITY, VERTICAL P.C.TAIL, MALE			
DRAWN DATE	11/20/2025				
CHECKED BY	R.S.M.	PART NUMBER MHHDD-XXMNS-X1			
CHECK DATE	11/21/2025				
TOLERANCES	ALL DIMENSIONS AND TOLERANCES IN MM	MATERIAL		SIZE	A
.X	± 0.3			REVISION	
.XX	± 0.25	SCALE 1:1		1	
.XXX	± 0.10			1 OF 1	