




Part Number : [510040500](#)
Product Description : 2.00mm Pitch MicroBlade
Wire-to-Board Housing, Friction Lock, 5.80mm Height,
5 Circuits
Series Number : 51004
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings
[510040500 sd.pdf](#)
Specifications
[PS-51004-002-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	51004
Description	2.00mm Pitch MicroBlade Wire-to-Board Housing, Friction Lock, 5.80mm Height, 5 Circuits
Application	Wire-to-Board
Product Name	MicroBlade
UPC	800753575943

Agency

CSA	LR19980
UL	E29179

Physical

Circuits (maximum)	5
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	145.200/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Stackable	No

Temperature Range - Operating	-20° to +85°C
-------------------------------	---------------

Mates With / Use With

Mates with Part(s)

Description	Part Number
MicroBlade Vertical Headers	<u>53014</u>
MicroBlade Right-Angle Headers	<u>53015</u>
MicroBlade Bottom Entry Headers	<u>53025</u>

Use with Part(s)

Description	Part Number
2.00mm Pitch MicroBlade Wire-to-Wire Crimp Terminals	<u>50011</u>

This document was generated on May 27, 2026