

MA2.5/5.D2



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks → SNA Series

General Information

Extended Product Type:	MA2.5/5.D2
Product ID:	1SNA115490R1300
EAN:	3472591154900
Catalog Description:	MA2.5/5.D2 Screw Clamp Terminal Blocks - Double deck - Grey
Long Description:	- Save space with double deck terminal blocks: 2 independent circuits connected in just 5 mm 0.200 in spacing, - Flexibility: snap onto symmetrical and asymmetrical rails.

Ordering

Color:	Grey
Minimum Order Quantity:	50 piece
Customs Tariff Number:	85369010

Popular Downloads

Data Sheet, Technical Information:	1SNC160019C0202
Instructions and Manuals:	1SNC160019C0202

Dimensions

Product Net Width:	5 mm
Product Net Height:	65.5 mm
Product Net Depth / Length:	52 mm
Product Net Weight:	15 g

Technical

Rated Cross-Section:	2.5 mm ²
Spacing:	5 mm
Connection Type:	Screw clamp
Function:	Feed-through
Number of Levels:	2
Connecting Capacity Main Circuit:	Screw Clamp / Flexible 1x 0.22 ... 2.5 mm ² Screw Clamp / Rigid 1x 0.2 ... 4 mm ²
Gauge Type:	A3
Rated Current (I_n):	Main Circuit 24 A
Rated Short-time Withstand Current (I_{cw}):	for 1 s 300 A
Rated Voltage (U_r):	630 V

Rated Impulse Withstand Voltage (U _{imp}):	8000 V
Dielectric Test Voltage:	2500 V
Pollution Degree:	3
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Wire Stripping Length:	9.0 mm
Recommended Screw Driver:	3.5 mm
Tightening Torque:	acc. IEC 60947-1 0.4 N·m Manufacturer 0.6 N·m

Technical UL/CSA

Maximum Operating Voltage UL/CSA:	Main Circuit 300 V
Connecting Capacity Main Circuit UL/CSA:	Screw Clamp / Rigid 1x 22 ... 12 AWG
Connecting Capacity UL/CSA:	Screw Clamp / Rigid 22 ... 12 AWG Stranded 12 AWG
Flammability According to UL94:	V0

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment

Certificates and Declarations (Document Number)

cUL Certificate:	1SND161000A0203
Declaration of Conformity - CE:	1SND225014U1000
EAC Certificate:	1SND161009A1100
Environmental Information:	1SND220002E1002
Instructions and Manuals:	1SNC160019C0202
RMRS Certificate:	1SND161007A1101
RoHS Information:	1SND230023F0208

Classifications

Object Classification Code:	X
E-number:	2925539
ETIM 4:	EC000897 - Feed-through terminal block

ETIM 5: EC000897 - Feed-through terminal block

ETIM 6: EC000897 - Feed-through terminal block

Container Information

Package Level 1 Units: 50 piece

Package Level 1 Width: 126 mm

Package Level 1 Depth / Length: 155 mm

Package Level 1 Height: 64 mm

Package Level 1 Gross Weight: 0.75 kg

Package Level 1 EAN: 3472591154900

Package Level 2 Units: 500 piece

Package Level 2 Width: 300 mm

Package Level 2 Depth / Length: 500 mm

Package Level 2 Height: 150 mm

Package Level 2 Gross Weight: 7.850 kg

Package Level 3 Units: 24000 piece

Product Packing Type: Box

