




D

C

B


A



REAR VIEW

DRAWING REVISIONS (RELEASE DATE ON FILE)			
REV	DOCUMENT	APP	APPROVAL DATE
E	PER CO# 839	V.R.	01/18/10

2.6 REF
[0.10]
SECONDARY LOCKS SHIPPED
IN PRE-STAGED POSITION



- NOTES:
- DIMENSIONS SHOWN IN MILLIMETERS [INCHES].
 - FOR WIRE SIZE APPLICATIONS, CONSULT FACTORY.
 - FEMALE TERMINALS TO BE ORDERED SEPARATELY: P/N'S 425 00 00 873/872.
 - PART MATES WITH CINCH HEADER CONNECTOR (CONSULT FACTORY).
 - SEAL PLUGS TO BE ORDERED SEPARATELY: P/N 581 00 00 011.
 - DRAWING TOLERANCES (UNLESS OTHERWISE SPECIFIED):
.X = ±0.5
.XX = ±0.25
 - SEALING RANGE FOR WIRE INSULATION DIAMETER:
MAXIMUM: 2.64MM [0.104"]; MINIMUM: 1.96MM [0.077"].
 - A TRIANGLE "▲" INDICATES A CHARACTERISTIC REQUIRING INSPECTION VERIFICATION.
 - IF TIE-WRAP DRESSING CONDUCTORS, CINCH RECOMMENDS A SPACING OF NO LESS THAN 50.8MM [2.00"] BEHIND THE BACK PLATE.

UNITS
METRIC

DO NOT SCALE DRAWING
UNLESS OTHERWISE SPECIFIED:
ALL DIMENSIONS ARE IN mm

CONFIDENTIAL
THIS DOCUMENT IS THE PROPERTY OF CINCH.
NEITHER THIS DOCUMENT NOR ANY OF
THE INFORMATION CONTAINED IN IT MAY
BE DUPLICATED OR DISCLOSED WITHOUT
PRIOR WRITTEN CONSENT OF CINCH.
©COPYRIGHT 2009 CINCH

DESIGN ENGINEER
A.CAINES

DATE
4/25/00

APPROVALS
ON FILE

CINCH
1700 FINLEY RD
LOMBARD, IL 60148

18 POSITION SOCKET CONNECTOR

MATERIAL
MATERIAL SPEC NUMBER
CAGE IDENT NO.
5810118023
71785

CONTROL SPEC NUMBER
PROJECT NUMBER
A14243

DRAWING NUMBER
5810118023S

SCALE
1.500

SHEET 1 OF 1