




REV.	DATE	ECR NO.	DESCRIPTION
NC	08/01/05	XXXXXX	INITIAL RELEASE
A	12/17/10	2128	CHANGE TITLE BLOCK FROM "RG-316U/D" TO "RG-179BD"



1. CRIMPED FERRULE
HEX CRIMP SIZE .151"
2. CONTACT PIN TO SOLDER

10	HEAT SHRINK TUBING			1
9	FERRULE	COPPER	GOLD	1
8	COVER	BRASS	GOLD	1
7	INSULATOR	PE	NATURAL	1
6	RETAINER RING	BER. COPPER	NATURAL	1
5	CONTACT PIN	BER. COPPER	GOLD	1
4	INSULATOR	PTFE	NATURAL	1
3	BARREL	BRASS	GOLD	1
2	BODY	BRASS	GOLD	1
1	SHELL	BRASS	GOLD	1
	DESCRIPTION	MATERIAL	FINISH	QTY

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex				
	DRAWN M.ZHANG		12/17/10						
	CHECKED				PART DESCRIPTION MINI 75 OHM SMB R/A CRIMP PLUG (FOR RG-179DB CABLE)				
	ISSUED								
	SHEET 1 OF 1								
					PART NO. 142176-75				
	CAD FILE		C:/CONNEX/142186-75.DWG						
					DWG. NO. 142176-75.DWG			REV. A	SIZE A