








NOTES:

1. MATERIALS:

HOUSING - THERMOPLASTIC, BLUE
SHELL - COPPER ALLOY, NICKEL PLATED
TERMINALS - COPPER ALLOY, GOLD PLATED ON CONTACT AREA
TIN PLATED ON SOLDER TAIL

2. ELECTRICAL CHARACTERISTICS:

CONTACT RESISTANCE - 30m OHMS MAX
INSULATION RESISTANCE - 1000M OHMS MIN @ 500V DC
CURRENT RATING - 1A MAX
DIELECTRIC WITHSTANDING - 500V AC FOR 1 MINUTE

3. OPERATION TEMPERATURE - -40°C TO +60°C

4. THIS PRODUCT IS RoHS COMPLIANT.

CUSTOMER DRAWING

					UNLESS OTHERWISE SPECIFIED 1. ALL DIMENSIONS IN INCHES [mm] - TWO PLACE DECIMALS ±0.02 [0.5] - THREE PLACE DECIMALS ±0.008 [0.20]	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.														
						SIZE	WIDTH		MULT		LBS/M		TEMPER							
						FINISH SPEC No.						MATERIAL SPEC No.								
						FIRST USED ON				SCALE 3:1		Switchcraft®								
						DATE DRAWN	BY	CHKD		APVD										
A	28548	10/26/22	PC	TJK		8/29/22	MK	TS 8/29/22		TJK 10/7/22										
REV	ECO NUMBER	DATE	BY	APVD	NAME						PART No.				REV					
REVISIONS					DO NOT SCALE DRAWING					RIGHT ANGLE USB TYPE-A 3.0, RoHS						RAHPC2UA30E				A