





B233045N2**

SERIES _____
 B23= FORM A
 POLES _____
 2= 2 POLE & 3= 3 POLE
 CURVED BASE DIAMETER _____
 040= Ø40, 045= Ø45, 050= Ø50, 060= Ø60, 080= Ø80, 100= Ø100, 160= Ø160,
 MATERIAL AND HOUSING COLOUR _____
 N= PA6 BLACK, W= PA6 BLACK V0
 SCREW AND GASKET _____
 2= NBR FLAT GASKET & SCREWS
 4= SILICON FLAT GASKET & SCREWS
 NON STANDARD COMPONENTS _____



ITEM	DESCRIPTION
1	INSERT
2	EARTH SCREW
3	TERMINALS
4	HOUSING
5	GASKET



NOTES
 1. PLEASE SEE TABLE FOR CURRENTLY CONFIGURED PART NUMBERS.
 FOR SPECIFIC PART NUMBERS PLEASE CONTACT SALES OR CONSULT
 THE INTELLIGENT PART NUMBERS IN THE TABLE ATTACHED.
 3. FOR PACKAGING SEE PACKAGING SPEC PK-121013-B23
 4. PRODUCT SPEC: SEE PS-121201-001
 4. TERMINALS BENT AFTER INSERTION FOR BEND ANGLE SEE TABLE

LAST INSPECTION NUMBER 4

PART No.	mPm PART No.	DESCRIPTION	TERMINAL BEND ANGLE (°)
1210120058	B233045N2	TYPE A 3P BLACK, Ø45 NBR FLAT GASKET & SCREWS	45
1210120060	B233050N2	TYPE A 3P BLACK, Ø50 NBR FLAT GASKET & SCREWS	45
1210120052	B232060N2	TYPE A 2P BLACK, Ø60 NBR FLAT GASKET & SCREWS	45
1210120050	B232045N2	TYPE A 2P BLACK, Ø45 NBR FLAT GASKET & SCREWS	45
1210120063	B233080N2	TYPE A 3P BLACK, Ø80 NBR FLAT GASKET & SCREWS	45
1210120062	B233060N4	TYPE A 3P BLACK, Ø60 SILICON FLAT GASKET & SCREWS	45
1210120061	B233060N2	TYPE A 3P BLACK, Ø60 NBR FLAT GASKET & SCREWS	45
1210120059	B233045N4	TYPE A 3P BLACK, Ø45 SILICON FLAT GASKET & SCREWS	45
1210120057	B233040N2	TYPE A 3P BLACK, Ø40 NBR FLAT GASKET & SCREWS	45
1210120055	B232100N2	TYPE A 2P BLACK, Ø100 NBR FLAT GASKET & SCREWS	45
1210120054	B232080N2	TYPE A 2P BLACK, Ø80 NBR FLAT GASKET & SCREWS	45
1210120051	B232050N2	TYPE A 2P BLACK, Ø50 NBR FLAT GASKET & SCREWS	45
1210120049	B232040N2	TYPE A 2P BLACK, Ø40 NBR FLAT GASKET & SCREWS	45
1210130232	B233100N2	TYPE A 3P BLACK, Ø100 NBR FLAT GASKET & SCREWS	45



ORIGINAL RELEASE EC NO: IPG2014-0532 DRAWN: KNOXMOYLE 2013/09/25 CHKD: OSHEA 2013-10-23 APPR: STGRIFFIN 2013/11/11	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION
				mm	INCH	DRAWN BY JOCONNOR	DATE 2011/06/22	TITLE B23 SERIES BASE	
			4 PLACES	± ---	± ---	CHECKED BY DMAHER	DATE 2011/06/22		
			3 PLACES	± ---	± ---	APPROVED BY EFOLAN	DATE 2011/07/12	MOLEX MOLEX INCORPORATED	
			2 PLACES	± 0.1	± ---	MATERIAL NO.			DOCUMENT NO.
			1 PLACE	± 0.2	± ---	SD-121012-005		SHEET NO. 1 OF 1	
			ANGULAR ± ---°		SEE CHART				
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A2		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		

SERIES _____

B20= FORM A BASE SERIES

POLES _____

2= 2 POLE & 3= 3 POLE

CURVED BASE DIAMETER _____

000 = FLAT

MATERIAL AND HOUSING COLOR _____

G= PA6 GRAY, N= PA6 BLACK, W= PA6 BLACK V0

GASKET & SCREWS _____

1= NBR INTEGRATED GASKET & SCREWS

2= NBR FLAT GASKET & SCREWS

4= SILICON FLAT GASKET & SCREWS

0= WITHOUT GASKET AND SCREWS

ADDITIONAL INFORMATION

UR= UL APPROVED


SA= UL LISTED

1. FOR SPECIFIC PART NUMBERS PLEASE CONTACT SALES
OR CONSULT THE INTELLIGENT PART NUMBERS IN THE TABLE ATTACHED



2. PRODUCT SPEC: SEE PS-121201-001


3. PACKAGING SPEC: SEE PK-121012-B20

Part No	MPM Part No	DESCRIPTION	BEND ANGLE
1210120013	B202000N2	PLATTE 2+ERDE 2-DIAGONAL	180°
1210120168	B202000W2SA	BAS202 NERA UL94 V0 UL LISTED	180°
1210120169	B203000W2SA	BAS203 NERA UL94 V0 UL	180°
1210120019	B203000N2	STD. BASE 3 POLE+EARTH FLAT	180°



B203 SERIES BASE



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
DIMENSION UNITS		SCALE		CURRENT REV DESC: REMOVED OBSOLETED PART NUMBER AS PER PCN#514494.		molex							
mm		1:1											
GENERAL TOLERANCES (UNLESS SPECIFIED)						B20 SERIES BASES							
ANGULAR TOL ± 2.0 °		EC NO: 770993											
4 PLACES ±		DRWN: RAVINR1		2023/11/09		PRODUCT CUSTOMER DRAWING							
3 PLACES ±		CHK'D: GGA		2023/12/25									
2 PLACES ± 0.1		APPR: GGA		2023/12/25		DOCUMENT NUMBER SD-121012-013							
1 PLACE ± 0.2		INITIAL REVISION:		DOC TYPE						DOC PART		REVISION	
0 PLACES ±		DRWN: DMAHER_WEU		2010/03/18						PSD		001	
		APPR: JWALLACE		2010/03/24		D1							
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION 		DRAWING A2-SIZE		SERIES 121012		MATERIAL NUMBER SEE TABLE					
						CUSTOMER GENERAL MARKET		SHEET NUMBER 1 OF 1					