

Part Number : 1724580412
Product Description : EXTreme Ten60Power Panel-to-Board Right-Angle Plug Assembly with Guide Pins, 2 Power Circuit, 12 Signal Circuits, 2 Power Circuit
Series Number : 172458
Status : Active
Product Category : PCB Headers and Receptacles

Documents and Resources

Drawings

1724580412_sd.pdf

PK-46437-003-001.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

SYM-172458-0412-001.zip

Specifications

1724520000-AS-000.pdf

PS-173693-001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS

Downloaded from Arrow.com.

- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	172458
Description	EXTreme Ten60Power Panel-to-Board Right-Angle Plug Assembly with Guide Pins, 2 Power Circuit, 12 Signal Circuits, 2 Power Circuit
Application	Panel-to-Board
Component Type	PCB Header
Keyword	Ten60
Product Name	EXTreme Ten60Power
UPC	889056069632

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	50.0A
Voltage - Maximum	600V AC / 250V DC

Physical

Downloaded from Arrow.com.

Breakaway	No
Circuits (Loaded)	16
Circuits (maximum)	16
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Gender	Male
Glow-Wire Capable	No
Guide to Mating Part	Side, Yes
Keying to Mating Part	No
Lock to Mating Part	No
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Liquid Crystal Polymer (LCP)
Mounting Style	Through Hole
Net Weight	17.918/g
Number of Rows	1, 3
Orientation	Right Angle
Packaging Type	Tray
PCB Retention	Yes
PC Tail Length	2.84mm
Pitch - Mating Interface	2.54mm, 7.50mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
(p)ower-(s)ignal Configuration	2p - 12s - 2p
Shrouded	Unshrouded
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Through Hole

Solder Process Data

Lead-Free Process Capability	SMC&WAVE

Downloaded from Arrow.com.

Max-Temp	260

Mates With / Use With

Mates with Part(s)

Description	Part Number
EXTreme Ten60Power Panel-to-Board Receptacle Housings	172512

Downloaded from Arrow.com.