



BA16EL6M, Terminal Vinyl Insulated
Locking Fork #16 AWG #6 Stud on Mylar
Reel

By Burndy
Catalog # BA16EL6M

BURNDY; VINYLUG; Terminal fork; RoHS Compatible; Wire Size:
#22-16 AWG; Material: Copper; Color: Red

Features

- Vinyl Locking Fork Tongue Terminals banded together on mylar carrier strip for high volume crimping
- Meets IEA-468-B standard
- Can be integrated with fully autonomous wire harness machines

Specifications

Certification - cULus	N
Certification - UL Recognized	N
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Copper Solid Size	• 20 • 18 AWG • 17 AWG • 16 AWG
Conductor - Copper Solid Size Range	20 -16 AWG
Conductor Size	22 - 16 AWG
Conductor - Copper Str Size	• 20 AWG • 18 AWG • 16 AWG
Conductor - Copper Str Size Range	20 AWG-16 AWG
Conductor Type	CU C Str-Size

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Locking Fork Terminal

Dimensions



Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Z inch	0.23 in
Dimension - Pad Width inch	0.28 in
Package Height	0.000 in
Length	0.87 in
Dimension - Hole Size fraction	7/50
Dimension - Bolt Size fraction	#6
Dimension - Hole Size inch	0.14 in
Dimension - Stud Size inch	#6
Dimension - Length Overall inch	0.87 in
Width	0.29 in
Height	0.29 in
Dimension - Thread Size	-
Dimensions	0.87 in x 0.29 in x 0.29 in

General

Insulation Type	Vinyl
Physical Attribute - Tongue Type	Locking Fork
Trade Name	VINYLUG
Plated	Y
Feature - Barrel Style	Shrouded
Insulation	Y
UPC 12 Digit	781810029312
UPC 14 Digit GTIN	00781810029312
Material	Copper
Plating Type	Tin
UPC	781810029312

Logistics

Minimum Pack Quantity	2000
-----------------------	------

Product Assets

[Catalog \[English\]](#)