

Search by SKU, Product Name or Keyword

SEARCH

CART



[Products](#) [Catalogs](#) [Free Samples](#) [Free CAD](#) [Knowledge Center](#) [Contact Us](#)

[Home](#)

[Fasteners](#)

[Rivets](#)

[Push-In Rivets](#)



Snap Rivet, Black, Nylon, UL94 V-2, .165 in Max Hole Dia., .354 in Min Panel Thk., .413 in Max Panel Thk.



In Stock



Item Code: SR-4120B

Black Snap Rivets. These Rivets have a .315 in head diameter, are compatible with a .161 - .165 in (4.1 - 4.2 mm) hole and go into a maximum panel thickness of .413 in

Description		Quantity	Options
Head Diameter	: .315 in (8 mm)	1000	Add to Cart Request CAD Free Sample Request Quote
Head Height	: .071 in (1.8 mm)		
Anchor Length	: .472 in (12 mm)		
Color	: Black		
Full Material	: Nylon 6/6		
Operating Temperature Range	: -40 - 239 °F (-40 - 115 °C)		
Brand	: Richco		
Compatible Hole Diameter Range	: .161 - .165 in (4.1 - 4.2 mm)		
Compatible Panel Thickness Range	: .354 - .413 in (9 - 10.5 mm)		
Series	: SR		
Material Flammability Standard	: UL94 V-2		

Downloads



Print Page

ESSENTIAL SOLUTIONS

DELIVERED

Abrasives & Grinding
Access Hardware
Adhesives, Sealants & Tapes
Bearings & Power Transmissions
Caps & Plugs

Clamps & Workholdings
Cutting & Machining
Extrusions & Structural Systems
Fasteners
Feet, Casters & Glides

Fiber, Wire & Cable Management
Flange Protection
Knobs, Handles & Grips
Material Handling
Shop Supplies

PCB & Electronics Hardware
Pneumatics & Hydraulics
Raw Materials
Tamper Evident & Security Seals
Tooling & Positioning Components
Tools & Precision Instruments



About Us

[About Essentra Components](#)
[About Essentra PLC](#)
[Locations](#)
[Knowledge Center](#)

Customer Service

[Contact Us](#)
[Catalogs](#)
[Sample Program](#)
[Free CAD](#)
[Careers](#)
[Distributor Portal](#)

Policies

[Privacy Policy](#)
[Terms and Conditions of Sale](#)
[Terms and Conditions of Purchase](#)
[Environmental Policy](#)
[Health and Safety](#)
[Quality Statement](#)

Terms of Use

[Website Terms of Use](#)
[Cookie Policy](#)



ABOUT SSL CERTIFICATES