



ON Semiconductor®

<http://onsemi.com>

2SK715

N-Channel JFET 15V, 5 to 24mA, 50mS, SPA

Applications

- AM tuner RF amp, low-noise amp
- HF low-noise amp

Features

- Adoption of FBET process
- Large $|y_{fs}|$
- Small Ciss
- Very low noise figure

Specifications

Absolute Maximum Ratings at Ta=25°C


Parameter	Symbol	Conditions	Ratings	Unit
Drain-to-Source Voltage	V_{DS}		15	V
Gate-to-Drain Voltage	V_{GDS}		-15	V
Gate Current	I_G		10	mA
Drain Current	I_D		50	mA
Allowable Power Dissipation	P_D		300	mW
Junction Temperature	T_j		125	°C
Storage Temperature	T_{stg}		-55 to +125	°C

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

Package Dimensions

unit : mm (typ)


7524-005




Product & Package Information

- Package : SPA
- JEITA, JEDEC : SC-72
- Minimum Packing Quantity : 2,500 pcs./box

Marking



Electrical Connection



Electrical Characteristics at Ta=25°C





Parameter	Symbol	Conditions	Ratings			Unit
			min	typ	max	
Gate-to-Drain Breakdown Voltage	V(BR)GDS	I _G =-10μA, V _{DS} =0V	-15			V
Gate-to-Source Leakage Current	I _{GSS}	V _{GS} =-10V, V _{DS} =0V			-1.0	nA
Zero-Gate Voltage Drain Current	I _{DSS} *	V _{DS} =5V, V _{GS} =0V	5.0*		24.0*	mA
Cutoff Voltage	V _{GS(off)}	V _{DS} =5V, I _D =100μA		-0.6	-1.4	V
Forward Transfer Admittance	y _{fs}	V _{DS} =5V, V _{GS} =0V, f=1kHz	25	50		mS
Input Capacitance	Ciss			10		pF
Reverse Transfer Capacitance	Crss			3.0		pF
Noise Figure	NF	V _{DS} =5V, R _G =1kΩ, I _D =1mA, f=1kHz		1.5		dB








* : The 2SK715 is classified by I_{DSS} as follows : (unit : mA)

Rank	T	U	V	W
I _{DSS}	5.0 to 8.5	7.3 to 12.0	10.0 to 17.0	14.5 to 24.0

Ordering Information

Device	Package	Shipping	memo
2SK715U-AC	SPA	2,500pcs./box	Pb Free
2SK715V-AC	SPA	2,500pcs./box	





Taping Specification


2SK715U-AC, 2SK715V-AC

Storage package Outline name	Package type	Maximum Number of devices contained(pcs.)		Packing format	
		Inner box No.	Storage quantity	Outer box (C-6)	Outer box (C-8)
SPA	A C	C-2 Inner box Dimensions :mm(external) 330×45×145	2,500	16 inner boxes contained(40,000pcs.) Outer box Dimensions:mm(external) 585×345×200	8 inner boxes contained(20,000pcs.) Outer box Dimensions:mm(external) 345×300×200
	A L	C-2 Inner box Dimensions :mm(external) 330×45×145	2,400	16 inner boxes contained(38,400pcs.) Outer box Dimensions:mm(external) 585×345×200	8 inner boxes contained(19,200pcs.) Outer box Dimensions:mm(internal) 345×300×200
	A P	C-4 Inner box Dimensions :mm(external) 330×45×285	5,000	8 inner boxes contained(40,000pcs.) Outer box Dimensions:mm(external) 585×345×200	4 inner boxes contained(20,000pcs.) Outer box Dimensions:mm(internal) 345×300×200
	A S	C-2 Inner box Dimensions :mm(external) 330×45×145	1,200	16 inner boxes contained(19,200pcs.) Outer box Dimensions:mm(external) 585×345×200	8 inner boxes contained(9,600pcs.) Outer box Dimensions:mm(internal) 345×300×200

1. Packing format


Packing method

Put zigzag folding in an inner box.



Sample bar code label


(Unit : mm)



* LEAD FREE 1 :
Lead-free external terminal surface treatment product.

2. Taping specifications

2-1. Carrier tape size (Unit:mm)




2-2. Taping size standard

Unit:mm

Item	Symbol	Standard	Tolerance	Item	Symbol	Standard	Tolerance
Work piece outside diameter	D	4.0	±0.2	Tape width	W	18.0	+1.0 -0.5
	E	2.2	±0.2	Adhesive tape	W0	6.0	±1.0
Work piece height	A	3.0	±0.2	Displacement of perforations	W1	9.0	+0.75 -0.5
Lead wire diameter	d	0.4×0.4 t	±0.1	Work piece bottom surface position	H	19.8	+1.0 -0.3
Bonded lead wire	l1	2.5MIN		Lead wire clinch height	H0	16.0	±0.5
Pitch between products	P	12.7	±1.0	Work piece upper limit position	H1	22.8	±1.5
Pitch between perforations	P0	12.7	±0.2	Perforations diameter	D0	φ4.0	±0.2
Total pitch for 21 perforations	P0×20	254.0	±1.0	Tape thickness (total thickness)	t	0.6	±0.2
Distance between lead wire	F	5.0	+0.8 -0.2	Product inclination	Δ c	0	±1.0
Lead wire pitch distance	F1	2.5	+0.4 -0.1				
Product inclination	Δ h	0	±2.0				
Displacement of perforations	P1	3.85	±0.3	To be measured at a position below the clinch			
	P2	6.35	±0.3				
Displacement of tape	W2	0.5MAX		Not to be displaced to the outside of the board			

2-3. Taping structure




- Provide an empty section for about three to five pieces in leading and end portions of the tape.
- Provide marking in red to the E-side end of the board.

2SK715

Outline Drawing

2SK715U-AC, 2SK715V-AC



ON Semiconductor and the ON logo are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of SCILLC's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.