




PC card drilling dimensions(after plating)
(thickness ≤ 3.20±0.30mm)



ROHS PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	D09S91C4GI00LF	D09S91C6GI00LF
15	39.14	33.32	25.18	24.54	19.18	D15S91C4GI00LF	D15S91C6GI00LF
25	53.03	47.04	39.12	38.25	33.12	D25S91C4GI00LF	D25S91C6GI00LF
37	69.32	63.50	55.68	54.71	49.68	D37S91C4GI00LF	D37S91C6GI00LF
						200 Mating	500 Mating

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C01-8646-0001

mat'l. code				surface	tolerance	projection	product family		
				ISO 1302	ISO 406 ISO 1101		D-SUB		
ltr	ecn no	dr	date	tolerances unless otherwise specified			title		
A	-	JAR	1996-09-17	angles	linear	.0±0.1	FEMALE CONNECTOR DELTA D EUROPE STRAIGHT PRESS-FIT		
B	LS05-004	MPE	2005-02-15			.00±0.1			
C	LS06-0097	LGO	2006-07-28	0°±2°		.000±0.1			
D	LS06-0140	LGO	2006-09-22	dr	PESSON	1996-09-17	dwg no		
E	111-0062	RPK	2011-04-05	engr	MITHUN PAUL	2016-06-06	sheet 1 of 1		
F	ELX-I-24020	AAB	2016-06-06	chr	ATHUL A.B	2016-06-06	C01-8646-0498		
				appd	BIJU K PAUL	2016-06-06	A3		
sheet index				revision	F		type Product Customer Drawing		
sheet				1					