

WE RECOMMEND THESE CONNECTORS FOR OPTIMAL SERVICE LEVEL



- SHORT LEAD-TIMES
- LOW MOQs
- QUICK SAMPLING
- AVAILABLE AT DISTRIBUTION



77313-101-04LF	77313-118-04LF
77313-101-06LF	77313-118-06LF
77313-101-08LF	77313-118-08LF
77313-101-10LF	77313-118-10LF
77313-101-12LF	77313-118-12LF
77313-101-14LF	77313-118-14LF
77313-101-16LF	77313-118-16LF
77313-101-18LF	77313-118-18LF
77313-101-20LF	77313-118-20LF

PLATING
1 = 0.76µm GOLD/GXT ON CONTACT AREA
2µm TIN MIN ON TAIL
1.27µm Ni MIN UNDERLAYER

PIN STYLE
SEE SHEET 3



RoHS COMPATIBLE
SEE NOTE 7

TOTAL NB OF POSITIONS

PACKAGING: - = POLYBAG

NOTES:

1. HOUSING MATERIAL : HIGH TEMPERATURE THERMOPLASTIC. UL94V-0 COLOR: BLACK
2. PIN MATERIAL : PHOSPHOR BRONZE
3. BERGSTIK PRODUCT PACKAGED IN BULK
BERGSTRIK PRODUCT PACKAGED PER REELS, SEE SHEET 2
4. 9N MIN RETENTION IN EITHER DIRECTION
5. TO DETERMINE DIMENSIONS :
N = NUMBER OF POSITIONS PER ROW
EXAMPLE : 8 POS N x 2.54 = 20.32mm
6. FOR PIN IN PASTE SOLDERING APPLICATION :
FINISHED PLATED HOLE Ø1.02-Ø1.06
LAND Ø1.45 MAX
7. RoHS COMPATIBLE PRODUCT SPECIFICATIONS
 - a - PLATING:
 - "LF" MEANS THE PRODUCT IS LEAD-FREE, 2µm MINIMUM MATTE TIN OVER 1.27µm MINIMUM NICKEL UNDERPLATE
 - b - MANUFACTURING PROCESS COMPATIBILITY
 - THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C ±5°C SOLDER BATH TEMPERATURE FOR 5 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.6mm MIN THICK CIRCUIT BOARD
 - REFLOW COMPATIBLE
 - c - LABELING:
 - MEETS PACKAGING SPECS AS PER GS-14-920
 - d - LEGAL STATEMENT: SEE GS-47-0004
8. THIS PART SERIES IS NOT INITIALLY INTENDED FOR AUTOMOTIVE APPLICATIONS. ADDITIONAL FEES ARE CHARGEABLE FOR ANY ADDITIONAL QUALIFICATION AND TEST REPORTS PERFORMED OUTSIDE THE SCOPE OF THE STANDARD PRODUCT SPECIFICATIONS.
9. UNLESS OTHERWISE APPROVED BY AMPHENOL, ALL PARTS AND COMPONENTS ARE DESIGNED & BUILT ACCORDING TO AMPHENOL'S SPECIFICATIONS WHICH ARE SUBJECT TO CHANGE WITHOUT NOTICE.



TOLERANCE "Z" DEPEND UPON
PIN MATING AND SOLDER LENGTHS

MATING/SOLDER LENGTH	ØZ	MATING/SOLDER LENGTH	ØZ
UP TO 10mm	Ø0.4	UP TO 14mm	Ø0.45
UP TO 18mm	Ø0.5	UP TO 22mm	Ø0.55
UP TO 26mm	Ø0.6	OVER 26mm	Ø0.65

mat'l. code SEE NOTES				surface ISO 1302	tolerance ISO 406 ISO 1101	projection mm	product family BERGSTIK
ltr	ecn no	dr	date	tolerances unless otherwise specified		mm	title UNSHR.HEADER STR DR TMT
CP	F-52796	DDE	24.09.04	angles	linear		
CR	F-54441	DDE	25.01.27		.XX ±0.3	scale 5:1	dwg no 77313
CS	F-55487	DDE	25.04.16		.XXX ±0.05		
CT	F-58161	DDE	25.11.14	dr	D.LEGRAND	01.01.24	sheet 1 of 3
CU	F-58402	DDE	25.12.01	enrg	J.COMPAGNON	01.01.24	
CV	F-28549	DDE	26.04.07	chr	J.COMPAGNON	01.01.24	size A3
				appd	J.COMPAGNON	01.01.24	
sheet index	revision	CV	BR	L			type CUSTOMER
	sheet	1	2	3			
							Drawing

Amphenol FCI

Copyright FCI

PRODUCT NUMBER
77313-YXX-XXLF

EXTENDED RANGE

PLATING, SEE BELOW
(AS AVAILABLE)

RoHS COMPATIBLE
SEE NOTE 7

TOTAL NB OF POSITIONS : 04 TO 72

PIN STYLE, SEE SHEET 3
(AS AVAILABLE)

OPTION LETTERS, SEE ON RIGHT
(MAY BE SUBJECT TO TOOLING FEES)


OPTIONS :

- = BULK PACKAGING
- "A" = TAPE & REEL WITH CAP, AS AVAILABLE
- "T" = STANDARD TUBE PACKAGING - ONLY AVAILABLE UPON REQUEST
- "V" = BLIBOX PACK FOR CUSTOMER DEDICATED PART
- "AV" = TAPE & REEL WITH CAP FOR CUSTOMER DEDICATED PART
- "KV" = TAPE & REEL WITHOUT CAP FOR CUSTOMER DEDICATED PART
- "TV" = TUBE WITHOUT CAP FOR CUSTOMER DEDICATED PART
- "R" = RETENTION FEATURE SHEET 4
IF RETENTION FEATURE "R" AND TUBE PACKAGING "T" ARE BOTH REQUIRED
OPTIONAL LETTER "R" WILL APPEAR INSTEAD OF THE FIRST DASH
EXAMPLE : 77313R118T40LF
- "KR" = T&R WITHOUT CAP WITH RETENTION FEATURE
- "ERP" = POLYBAG PACKAGING FOR DEDICATED CUSTOMER, WITH SPECIFIC LABEL

PLATING :

- 1 = 0.76µm GOLD/GXT ON CONTACT AREA, 2µm TIN MIN ON TAIL
- 4 = 2µm TIN MIN FULL PLATED
- 8 = 0.38µm GOLD/GXT ON CONTACT AREA, 2µm TIN MIN ON TAIL
- 9 = GOLD FLASH ON CONTACT AREA, 2µm TIN MIN ON TAIL
- G = 0.76µm FULL GXT
- S = 0.38µm FULL GXT
- T = 2µm TIN MIN FULL PLATED INCLUDED PIN TYP
- 1.27µm NICKEL MIN UNDERLAYER FOR ALL PLATING VERSIONS

RETENTION OPTION



NOTES :

- PART NUMBER 77313-YXXRXXLF
- 4 PINS "A" USED FOR RETENTION
DIRECTION OF RETENTION SHOWN BY ARROWS
PIN "A" AT EACH END OF HEADER.
- FOR RETENTION OPTION , SOLDER TAIL LENGTH TO BE
2.9 MIN UP TO 3.5 MAX.

PRODUCT NUMBER (BERGSTRIK PACKAGING)
77313-YXX-00LF


PLATING

- 1 = 0.76µm GOLD/GXT ON CONTACT AREA, 2µm TIN MIN ON TAILS
- 8 = 0.38µm GOLD/GXT ON CONTACT AREA, 2µm TIN MIN ON TAILS
- 4 = 2.0µm TIN MIN FULL PLATED
- 1.27µm NICKEL MIN UNDERLAYER FOR ALL PLATING VERSIONS

INDICATES THE PRODUCT IS RoHS
COMPATIBLE, SEE NOTE 7

POSITIONS PER REEL : 00=45,000 (BERGSTRIK)

PIN STYLE	MATING	SOLDER	OAL
01	5.84	2.41	10.8
02	5.84	3.42	11.8
18	5.84	3.05	11.43
22	7.75	3.05	13.35
24	6.75	2.9	12.2
27	6.6	2.66	11.8



BERGSTRIK HEADER REEL PACKAGING DIMENSIONS

mat'l. code				surface ISO 1302	tolerance ISO 406 ISO 1101	projection mm	product family BERGSTIK
ltr	ecn no	dr	date	tolerances unless otherwise specified			title
BM	F-47089	DDE	23.01.23	angles	linear	mm	UNSHR.HEADER
BN	F-54441	DDE	25.01.27			scale N/A	STR DR TMT
BP	F-58161	DDE	25.11.14				dwg no
BR	F-58402	DDE	25.12.01	dr	D.LEGRAND	01.01.24	sheet 2 of -
				engr	J.COMPAGNON	01.01.24	size
BK	F-22605	BVE	15.11.24	chr	J.COMPAGNON	01.01.24	77313
BL	F-45578	DDE	22.08.05	appd	JF.NOTTEAU	01.01.24	A3
sheet	revision						type
index	sheet						CUSTOMER Drawing

