RC-12P1N8D0000 - Contact insert

1597635

https://www.phoenixcontact.com/ae/products/1597635

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert, M23, number of positions: 12, contact connection type: Pin, Crimp connection, series: NC, RC, RM, TU, UC, this item is expected to be lead-free from Q4 2025 in accordance with RoHS II without exception 6c (Pb < 0.1%), a lead-free alternative is possible on request in advance

Commercial data

Item number	1597635
Packing unit	1 pc
Minimum order quantity	10 pc
Sales key	AB
Product key	ABRAFU
GTIN	4046356217217
Weight per piece (including packing)	10 g
Weight per piece (excluding packing)	3.278 g
Customs tariff number	85389099
Country of origin	DE

Downloaded from Arrow.com.

Technical data

Product properties

Product type	Contact insert
Series	NC
	RC
	RM
	TU
	UC
Application	Signal
Number of positions	12
Connection profile	12
Coding	N
Thread type	M23

Electrical properties

Contact: Contact group 1

Contact diameter	1 mm
Min. cross section	0.14 mm²
Max. cross section	0.56 mm²
Nominal current I_N	8 A (for max. connection cross section)
Nominal voltage U_N	48 V AC
	74 V DC
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	1.5 kV

Connection data

Connection method	Crimp connection

Material specifications

Material Insulating body	PA 6.6
Material Contact	CuZn
Material Contact surface	Ni/Au

Connector

Direction of rotation	Standard

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	50

Environmental and real-life conditions

Downloaded from Arrow.com.


Ambient conditions

Permissible humidity (storage/transport)	50 % ... 65 %

Downloaded from Arrow.com.

Drawings


Schematic diagram



Connector pin assignment

Downloaded from Arrow.com.

Schematic diagram



Dimensional drawing

Downloaded from Arrow.com.

Classifications

ECLASS

ECLASS-13.0	27440223
ECLASS-15.0	27440223

ETIM

ETIM 9.0	EC003557

UNSPSC

UNSPSC 21.0	39121400

Downloaded from Arrow.com.

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	e4d2d8bb-54a7-439a-b22f-2e3e3f484415

Phoenix Contact 2025 © - all rights reserved
https://www.phoenixcontact.com

PHOENIX CONTACT Middle East FZ LLC
1201N-1206N, Dubai Science Park Towers – North
P.O. Box 345002, Dubai, United Arab Emirates
(+971) 4 437-0324
info-me@phoenixcontact.com

Downloaded from Arrow.com.