

Terminal Part Number: 15494340
Surface Plating: SN
Material Thickness [mm]: -
Cross Section [mm²]: 1,50 | 2,50

This document is non-contractual
and for information only.

For more information, please
consult your local sales office

Cable Type codes: 2010
Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
Insulation Range Φ[mm]: 2,00 - 3,00
Seal(s): 10737670 | 15339838

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
2010 1,50 / 10737670		2,20	200	1,60	0,05	2,60	0,10	3,60	0,10	4,30	0,10
2010 1,50 / 15339838		2,20	200	1,60	0,05	2,60	0,10	3,90	0,10	4,25	0,10
2010 2,50 / 10737670		2,80	250	1,90	0,05	2,60	0,10	3,90	0,10	4,40	0,10
2010 2,50 / 15339838		2,80	250	1,90	0,05	2,60	0,10	4,20	0,10	4,45	0,10

Cable type code legend:

2010: ACW0219, FIAT T2 FLRY, FL RENAULT R1, FL RENAULT R3, FLR (AGP0219), FLR2X-A, FLR4Y-A, FLR9Y, FLRX-B, FLRY-A, FLRYB, FLRY-B



Industry Designator: DIN

Conductor Material: COPPER

Conductor Plating: NONE

Insul. Material: PA, POLYOLEFIN, PP, PVC, SYNTHRESIN, XLCOPOLY, XLPBT, XLPE, XLPE/PVDF, XLPVC

Insul. Wall Designator: THIN



Terminal Part Number: 15494340
Surface Plating: SN
Material Thickness [mm]: -
Cross Section [mm²]: 1,50 | 2,00 | 2,50

This document is non-contractual
and for information only.


For more information, please
consult your local sales office

Cable Type codes: 2053
Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
Insulation Range Φ[mm]: 2,10 - 2,90
Seal(s): 10737670 | 15339838

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
2053 1,50 / 10737670		2,18	200	1,60	0,05	2,60	0,10	3,60	0,10	4,30	0,10
2053 1,50 / 15339838		2,18	200	1,60	0,05	2,60	0,10	3,40	0,10	4,20	0,10
2053 2,00 / 15339838		2,40	230	1,75	0,05	2,60	0,10	3,90	0,10	4,30	0,10
2053 2,00 / 10737670		2,40	230	1,75	0,05	2,60	0,10	3,80	0,10	4,30	0,10
2053 2,50 / 10737670		2,80	250	1,90	0,05	2,60	0,10	4,00	0,10	4,40	0,10
2053 2,50 / 15339838		2,80	250	1,90	0,05	2,60	0,10	4,20	0,10	4,40	0,10

Cable type code legend:

2053: PSA T2 ZH ID, PSA T3 ZH ID, PSA T4 ZH ID
Industry Designator: PSA
Conductor Material: COPPER
Conductor Plating: NONE
Insul. Material: POLYOLEFIN, X-POLY
Insul. Wall Designator: ID



Terminal Part Number: 15494340
Surface Plating: SN
Material Thickness [mm]: -
Cross Section [mm²]: 1,50 | 2,00 | 2,50

This document is non-contractual
and for information only.



For more information, please
consult your local sales office

Cable Type codes: 2054
Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
Insulation Range Φ[mm]: 2,10 - 3,00
Seal(s): 15339838 | 10737670

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
2054 1,50 / 15339838		2,25	200	1,60	0,05	2,60	0,10	3,90	0,10	4,30	0,10
2054 1,50 / 10737670		2,25	200	1,60	0,05	2,60	0,10	3,80	0,10	4,25	0,10
2054 2,00 / 15339838		2,65	230	1,75	0,05	2,60	0,10	4,00	0,10	4,40	0,10
2054 2,00 / 10737670		2,65	230	1,75	0,05	2,60	0,10	3,90	0,10	4,30	0,10
2054 2,50 / 10737670		2,83	250	1,90	0,05	2,60	0,10	4,00	0,10	4,45	0,10
2054 2,50 / 15339838		2,83	250	1,90	0,05	2,60	0,10	4,10	0,10	4,50	0,10

Cable type code legend:

2054: PSA T2 IR, PSA T3 IR, PSA T3 ZH IR, PSA T4 LH IR
Industry Designator: PSA
Conductor Material: COPPER
Conductor Plating: NONE
Insul. Material: POLYOLEFIN, PVC, X-POLY
Insul. Wall Designator: IR



Terminal Part Number: 15494340
Surface Plating: SN
Material Thickness [mm]: -
Cross Section [mm²]: 2,00

*This document is non-contractual
and for information only.*

*For more information, please
consult your local sales office*

Cable Type codes: 3003
Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
Insulation Range Φ[mm]: 2,50 - 2,80
Seal(s): 15366064

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
3003 2,00 / 15366064		2,65	180	1,70	0,05	2,60	0,10	3,80	0,10	4,30	0,10

Cable type code legend:

3003: AVSS
Industry Designator: JIS/JA
Conductor Material: COPPER
Conductor Plating: NONE
Insul. Material: PVC, X-PVC
Insul. Wall Designator: THIN

