



Part Number : [22284054](#)
Product Description : KK 254 Breakaway Header, Vertical, 5 Circuits, 0.38µm Gold (Au) Selective Plating, Mating Pin Length 8.13mm
Series Number : 42375
Status : Active
Product Category : PCB Headers and Receptacles
Engineering Number : 42375-0145



Documents & Resources

Drawings
[022284054_sd.pdf](#)
[PK-40873-0041-001.pdf](#)

3D Models and Design Files
[022284054_stp.zip](#)

Specifications
[PS-10-07-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 33; 44; 34
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	42375
Description	KK 254 Breakaway Header, Vertical, 5 Circuits, 0.38μm Gold (Au) Selective Plating, Mating Pin Length 8.13mm
Application	Board-to-Board, Signal, Wire-to-Board
Component Type	PCB Header
Product Name	KK 254
UPC	800754386357

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	500V

Physical

Breakaway	Yes
Circuits (Loaded)	5
Circuits (maximum)	5
Color - Resin	Black
Durability (mating cycles max)	100

First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	0.343/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Bag
PC Tail Length	3.05mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Pitch - Mating Interface	2.54mm
Plating min - Mating	0.381µm
Plating min - Termination	2.540µm
Polarized to Mating Part	No
Polarized to PCB	No
Shrouded	No
Stackable	No
Temperature Range - Operating	See Product Specification
Termination Interface Style	Through Hole

Solder Process Data

Max-Duration	5
Lead-Free Process Capability	WAVE
Max-Cycle	1
Max-Temp	260

Mates With / Use With

Mates with Part(s)

Description	Part Number
KK 254 Single Row Crimp Housings	<u>2695</u>
KK 254 Receptacle Housings	<u>7880</u>
KK 254 PC Board Connector	<u>4455</u>
2.54mm Pitch C-Grid Shunt Terminal Housings	<u>7859</u>

This document was generated on Feb 07, 2025