


2P mark



N = Number of poles

Dim A=Nx5.08

Dim B=(N-1)x5.08

	Dim A	Dim B
2-6p	±0.15	±0.10
7-12p	±0.20	±0.20
13-18p	±0.30	±0.25
19-24p	±0.40	±0.30

SIGN	DATE	DESCRIPTION	APPROVER
△	02/08'07	Part No. is changed.	Aaron
△	04/08'09	Current rating, wire range and operating temperature are changed	Jacke
△	04/08'09	Add UL standard	Jacke
△	11/25'09	The Grey code changed from RAL7004/P to RAL7035/D	Kind
△	03/13'10	Add the 2P mark	RUNNER
△	07/25'13	update the drawing	Da cheng
THIS IS CAD DRAWING, DO NOT REVISE MANUALL Y!!!			

## Material

- Item 1 Terminal body:Thermoplastic ( UL94V-0 )
- △●Item 2 Terminal lever:Thermoplastic ( UL94V-0 ) Orange(RAL 2011/P)
- Item 3 Female contact:PhBz ( CuSn ) Tin plated

## Electrical cULus


- Voltage rating:300V
- △●Current rating:7A
- Wire range:
  - Solid wire(AWG):18-22
  - Stranded wire(AWG):18-22
- Wire strip length:
- Withstanding Voltage:1.6KV
- Operating temperature:-40°C to +115°C
- △●Safety Approval: cULus
- △●Critical dimension:

HP xx 50 x 0 xxxx G			RoHS compliant △△ (lead<4%) In copper Alloy
Poles	△ Body Color	0000 Standard @ Logo	
02 2Contacts	0 Black	000A Standard ANY Logo	
03 3Contacts	5 Green ( RAL 6018/T )	Any special item by	
..	6 Blue	customer request,	
24 24Contacts	△8 Grey ( RAL 7035/D )	please contact sales	
	C Green ( RAL 6018/U )	department.	

# ANYTEK

## CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		HP 5.08mm Series Without flange					
PART NO.	HPxx50x0xxxxG			DWG NO.	8HP0001		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance		
		Dacheng 2013.07.25	Dacheng 2013.07.25		UNIT: mm	X. ±0.50	
					SCALE: NONE	X.X ±0.30	
				SHEET: 01/01		REV.: I	X.XX ±0.10
							X° ±1°