

Home: >

Part Number: 57294-2011

ANVIL 87421

Image not available

Status: Active
Series: 57294
Category: Molex Parts

Go to Part Detail

CHECK DISTRIBUTOR INVENTORY

Add to My Parts

Series image - Reference only

Note - Please disable browser pop-up blockers to view documents on www.molex.com

Product Environmental Compliance

- EU ELV:Not Reviewed
- EU RoHS:Not Reviewed
- EU RoHS Phthalates:Not Reviewed
- China RoHS:Not Reviewed
- REACH SVHC:Not Reviewed
- Low-Halogen Status:Not Reviewed

- Product Compliance Statement
- EU RoHS Certificate of Compliance (PDF)
- Multiple Part Product Compliance Statements
EU RoHS, REACH SVHC, & Low-Halogen
- Multiple Part Industry Compliance Documents
*IPC 1752A Class C
*IPC 1752A Class D

*Molex Product Compliance Declaration

Questions on Product Environmental Compliance? EmailProductCompliance@molex.com
Request Molex's CMRT from conflictminerals@molex.com

Application Tooling FAQ

Tooling specifications and manuals are found by selecting the products below.
Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling
Check our list of old tooling that used to be available for this part

Part Detail

COLLAPSE ALL

General

Table with 2 columns: Attribute (Status, Category, Series, UPC) and Value (Active, Molex Parts, 57294, 822350834230)

PRODUCTS++

- Product Categories
- Product Index
- Industries

QUICK LINKS++

- Company Information
- Contact Molex
- Cross-Reference
- Koch Industries
- Investor Relations
- Literature
- Press Room / Press Releases
- Sitemap
- Terms & Conditions

RESOURCES++

- Supply Chain Transparency
- Business Continuity
- Compliance
- ecocare
- Feedback | Help
- Jobs
- Legal | Trademarks
- Supplier Portal
- Privacy Policy
- Tradeshows

STAY CONNECTED



Molex is a registered trademark of Molex, LLC in the United States of America and may be registered in other countries; all other trademarks listed herein belong to their respective owners.

© Copyright 2018