

## M8 PFT straight 0,5m



Image is for illustration purposes only. Please refer to product description.

Part number	21 02 357 6405
Specification	M8 PFT straight 0,5m
HARTING eCatalogue	<a href="https://harting.com/21023576405">https://harting.com/21023576405</a>

### Identification

Category	Connectors
Series	Circular connectors M8
Element	Panel feed through
Specification	With conductors for front mounting

### Version

Gender	Female
Shielding	Unshielded
Number of contacts	4
Coding	A-coding
Locking type	Screw locking

### Technical characteristics

Conductor cross-section	0.25 mm <sup>2</sup>
Conductor cross-section [AWG]	AWG 24
Rated current	3 A
Rated voltage	30 V
Rated impulse voltage	1.5 kV
Pollution degree	3
Overvoltage category	III
Insulation resistance	>10 <sup>8</sup> Ω
Contact resistance	≤10 mΩ



Pushing Performance  
Since 1945

## Technical characteristics

Tightening torque	0.8 Nm Lock nut
Limiting temperature	-30 ... +80 °C
Mating cycles	≥100
Degree of protection acc. to IEC 60529	IP67
Isolation group	I (600 ≤ CTI)
Conductor length	50 cm

## Material properties

Material (insert)	Thermoplastic polyurethane (TPU)
Material (contacts)	Brass
Surface (contacts)	Au over Ni Mating side
Material (hood/housing)	Copper-zinc alloy
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	0d7d3693-d625-47ab-934a-d241bf72c86e
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

## Specifications and approvals

Specifications	IEC 61076-2-104
UL / CSA	UL 2238 CYJV2.E302521 CSA-C22.2 No. 182.3 CYJV8.E302521
Approvals	CE

## Commercial data

Packaging size	1
Net weight	14.7 g
Country of origin	Czechia



**Pushing Performance**  
Since 1945

## Commercial data

European customs tariff number	85444290
GTIN	5713140136984
eCl@ss	27440103 Sensor-actuator connector chassis (sensor technology actuator)
UNSPSC 24.0	39121413